

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 15 ft. (4.57 m)

MODEL NUMBER: P560-015



Description

This DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection.

Use in conjunction with DVI video cards that are specified as Dual Link. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- DVI-D Dual Link Male-Male, 15-ft. (4.57 m)
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- · Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- Supports 2560 x 1600 resolution
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW		
UPC Code	037332149947	
Product Type	Passive Cable	
Technology	DVI	
Cable Type	Passive	
PHYSICAL		

Highlights

- DVI-D Dual Link TMDS Male-Male, 15ft
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

 Monitor with DVI, and CPU with Dual Link DVI capabilities

Package Includes

DVI Dual Link TMDS cable - DVI-D, M/M, 15-ft. (4.57 m)



Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	15	
Cable Length (m)	4.57	
Cable Length (in.)	180	
Shipping Dimensions (hwd / in.)	8.20 x 10.80 x 1.50	
Shipping Dimensions (hwd / cm)	20.83 x 27.43 x 3.81	
Shipping Weight (lbs.)	0.90	
Shipping Weight (kg)	0.41	
Unit Dimensions (hwd / in.)	8.200 x 10.800 x 1.500	
CONNECTIONS		
Side A - Connector 1	DVI-D DUAL LINK (MALE)	
Side B - Connector 1	DVI-D DUAL LINK (MALE)	
Latching or Gripping Connector	No	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.