



Terminals & Splices > Splices



Wire Size: 20 – 16 AWG
Sealable: Yes
Splice Capacity: 1
Splice Features: Splice Kit
Contact Base Material: Copper Alloy

Features

Product Type Features

Splice Accessory Type	Splice
Sealable	Yes

Configuration Features

Splice Capacity	1
-----------------	---

Body Features

Splice Features	Splice Kit
-----------------	------------

Contact Features

Contact Base Material	Copper Alloy
Barrel Type	Closed

Dimensions

Wire Size	20 – 16 AWG
-----------	-------------

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]

Industry Standards

Government Qualified Splice	No
-----------------------------	----



Packaging Features

Packaging Method	Bag/Box
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts










TE Part # 992008-000

AD-1377-CRIMP-TOOL-3-CVTY

Customers Also Bought



 <p>TE Part #DT04-2P REC, 2P, GRY, N</p>	 <p>TE Part #DT06-2S PLG, 2P, GRY, N</p>	 <p>TE Part #W2S Wedgelocks: DEUTSCH DT</p>	 <p>TE Part #0462-201-16141 DEUTSCH Solid Contacts</p>
 <p>TE Part #282104-1 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING</p>	 <p>TE Part #281934-2 SINGLE WIRE SEAL</p>	 <p>TE Part #114017-ZZ SEALING PLUG, SIZE 12/16, WHT</p>	

Documents

Product Drawings

D-200-0229

English

Datasheets & Catalog Pages

1654025_Sec8_D-200

English

Harness Repair Products Quick Reference Guide

English

Product Specifications

Instulation Procedure for D-200 series Shielded Cable Splice Kits with MiniSeal Crimp Primary Splices

English