

ATGBICS DAC-Q56-200G-1M Dell Compatible Direct Attach Copper Twinax Cable 200G QSFP56 (1m, Passive)

Brand : ATGBICS

Product code: DAC-Q56-200G-1M-C

Product name : DAC-Q56-200G-1M Dell Compatible Direct Attach Copper Twinax Cable 200G QSFP56 (1m, Passive)

DAC-Q56-200G-1M Dell Compatible Direct Attach Copper Twinax Cable 200G QSFP56 (1m, Passive)

ATGBICS DAC-Q56-200G-1M Dell Compatible Direct Attach Copper Twinax Cable 200G QSFP56 (1m, Passive):

ATGBICS DAC-Q56-200G-1M compatible 200GBase-CU QSFP56 to QSFP56 direct attach cable operates over passive copper with a cable length of 1m. It is suitable for short reach connection between two QSFP56 ports in 200G interconnecting networking applications. Our product meets the specification of Dell DAC-Q56-200G-1M= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols including; QSFP56 MSA, IEEE 802.3cd, SFF-8661, SFF-8636, SFF-8417, SFF-8679.

ATGBICS DAC-Q56-200G-1M Dell Compatible Direct Attach Copper Twinax Cable 200G QSFP56 (1m, Passive). Cable length: 1 m, Connector 1: QSFP56, Connector 2: QSFP56, Data transfer rate: 200000 Mbit/s



Features		Features	
Product colour *	Black	Certification	CE, FCC, RoHS
Cable length *	1 m	Country of origin	United Kingdom
Connector 1 *	QSFP56	Operational conditions	
Connector 2 *	QSFP56	Operating temperature (T-T)	0 - 70 °C
Connector 1 gender *	Male	Storage temperature (T-T)	-40 - 80 °C
Connector 2 gender *	Male	Operating relative humidity (H-H)	10 - 90%
Jacket material	Polyvinyl chloride (PVC)	Storage relative humidity (H-H)	10 - 85%
Conductor material	Copper	Packaging data	
Ethernet interface type	200 Gigabit Ethernet	Quantity per pack	1 pc(s)
Networking standards	IEEE 802.3cd	Technical details	
AWG wire size	30	Sustainability certificates	RoHS
Data transfer rate	200000 Mbit/s		
Plug and Play	✓		



5056468760203

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date