




TE Internal #: 1-2273012-3
M8 Pigtail Cable Assembly, 4 Position, 5 m, Sensor/Actuator, Code
A, M8 Socket, Single Ended, Plastic
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 Pigtail, Right Angle, LED



M8/M12 Application Type: **Sensor/Actuator**
Number of Positions: **4**
Connector & Keying Code: **A**
Connector Type (End A): **M8 Socket**
Cable Assembly Type: **M8 Pigtail**

[All M8 Pigtail, Right Angle, LED \(8\)](#)

Features

Product Type Features

Connector Type (End A)	M8 Socket
Cable Assembly Type	M8 Pigtail

Configuration Features

Status Indicator Type	LED
Number of Positions	4

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------

Body Features

Cable Color	Black
Connector Color (End A)	Black
Jacket Material	PVC
Wire Color (Base)	Brown, White, Blue, Black
Connector & Keying Code	A

Contact Features

Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Thread Size	M8
-------------	----



Connector Orientation (End A)

Right Angle

Housing Features

Housing Material	Plastic
------------------	---------

Dimensions

Outside Cable Diameter	4.5 mm[.177 in]
Wire Size	.326 mm ²

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Operation/Application

M8/M12 Application Type	Sensor/Actuator
Shielded	No

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Other

Field Serviceable	Yes
Cable Assembly Length	5 m
Cable Assembly Configuration	Single Ended

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T4051210003-005
M8 CABLE RA MALE 5M 3P PVC
CABLE

Customers Also Bought

TE Part #640907-1
PIDG FASTON Receptacle Quick
Disconnects

TE Part #1-1623774-8
C14 15K 5% (LOOSE)

TE Part #1102855-3
AWZG-HVT-RSZ

TE Part #NB14882001
DWP-125-1/8-0-STK

TE Part #1102855-7
AWZG-HE-Q5-RSZ

TE Part #1102855-5
AWZG-HSS-RSZ

TE Part #3042610142
Speed sen DSE 1810.38 PHZ
HZTL222755 R1

TE Part #3512606867
voltage I HZTL446144R0001



Documents

Product Drawings

M8 x 1.0 Angled socket Pigtail LED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2273012-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2273012-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2273012-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8 / M12 Connector System Catalog

Japanese

Product Specifications

Application Specification

English