

**Ratings**  
Voltage: 150 V  
Temperature: -40~70 °C

**Conductor**  
Conductor count: 7  
Gauge: 22 AWG 0.33 mm<sup>2</sup>  
Material: Tinned copper strands  
Strand size:  $\varnothing 0.08 \times 65$   
Resistance at 20 °C: 59.4 $\Omega$  /km max


**Insulator**  
Material: HDPE  
Color: white, black, red, yellow, blue, green, orange  
Diameter:  $\varnothing 1.25 \pm 0.10$  mm  
Nominal thickness: 0.24 mm  
Resistance at 20 °C: 100 M $\Omega$  /km min

**Wrap**  
Material: cotton paper

**Filler**  
Material: aramid fiber

**Outer jacket**  
Material: TPU  
Color: white  
Diameter:  $\varnothing 5.1 \pm 0.25$  mm  
Nominal thickness: 0.6 mm

**Tests**  
Tensile strength: 26 kgf min  
Dielectric test: 1500 V dc for 1 minute without breakdown  
Bend test at 200 g,  $\pm 60^\circ$ , 30 cycles /min: 15,000 cycle minimum



|           |           |                 |                                                                                                              |                                                                                                                                                                    |                                                                                                                 |  |                          |
|-----------|-----------|-----------------|--------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--|--------------------------|
| Revision: | Date:     | Description:    | Prepared:                                                                                                    | Notes:<br><br>RoHS compliant<br>Jacket meets ISO 10993 Biological Compatibility<br>Phthalate and halogen free<br>Function test: no open, no short, no intermittent | <div>TENSILITY</div> <div> tel 1.541.323.3228 800 877.670.7118<br/> fax 1.541.323.4202 web tensility.com </div> |  |                          |
| A         | 8/23/2022 | Initial release | Verified:                                                                                                    |                                                                                                                                                                    |                                                                                                                 |  |                          |
|           |           |                 | Dimensions are in millimeters.<br>Tolerances:<br>X: $\pm 0.5$ mm<br>X.X: $\pm 0.3$ mm<br>X.XX: $\pm 0.05$ mm | Description:<br>Wire, 7C TS, 22 AWG, 150V, 70C, 5.1 mm, TPU, 75A, white, WBL                                                                                       | Size: A                                                                                                         |  | Part number:<br>30-02816 |
|           |           |                 |                                                                                                              |                                                                                                                                                                    | Scale: 12:1                                                                                                     |  | Sheet 1 of 1             |
|           |           |                 |                                                                                                              |                                                                                                                                                                    |                                                                                                                 |  |                          |