


## Product: [1410R](#)

Audio Snake Cable, #24-8pr, TC, Indiv. Shielded, CMR



### Product Description

Audio Snake Cable, 8-24 AWG tinned copper pairs, polyolefin insulation, individually shielded with Beldfoil® bonded to numbered/color-coded PVC jackets so both strip simultaneously, overall Beldfoil® shield, drain, PVC jacket

### Technical Specifications

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.024 in	8

Conductor Count:	16
Total Number of Pairs:	8

##### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.04 in	0.008 in

##### Color Chart

Number	Color
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Purple
8	Gray
1	Red
2	Black

##### Inner Shield

Type	Material	Material Trade Name	Coverage (%)	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.024 in	24	7x32

##### Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.113 in	0.015 in

##### Outer Shield

Type	Material	Material Trade Name	Coverage (%)	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.046 in	18	7x26

##### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.446 in	0.038 in	Yes

## Electrical Characteristics

### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR
15.9 Ohm/1000ft	23.3 Ohm/1000ft	23.3 Ohm/1000ft	6 Ohm/1000ft

### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
31 pF/ft	58 pF/ft

### Inductance

Nominal Inductance
0.18 $\mu$ H/ft

### Impedance

Nominal Characteristic Impedance
50 Ohm

### Delay

Nominal Velocity of Propagation (VP) [%]
66%

### Current

Max. Recommended Current [A]
1.05 Amps per Conductor at 25°C

### Voltage

UL Voltage Rating
300 V RMS

### Temperature Range

Operating Temperature Range:	-30°C To +75°C
------------------------------	----------------

## Mechanical Characteristics

Bulk Cable Weight:	114 lbs/1000ft
Max. Pull Tension:	154 lbs
Min. Bend Radius/Minor Axis:	4.5 in

### Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Riser
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
1410R 010500	Black	Reel	500 ft	612825114840
1410R 0101000	Black	Reel	1,000 ft	612825114833

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Pair jackets and shields bonded so both strip simultaneously. Beldfoil® provides high reliability with ease of termination.
--------	---

## History

Update and Revision:	Revision Number: 0.425 Revision Date: 12-19-2022
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.