

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Moulded EMI Gasket Conductive Sheet

Gasket Type: **Moulded EMI Gasket**Finished Type: **Conductive Sheet**Binding Material: **Fluorosilicone**Filler Material: **Nickel Plated Graphite (Ni/C)**Gasket Shape: **Sheet**[All Moulded EMI Gasket Conductive Sheet \(36\)](#)

Features

Product Type Features

Finished Type	Conductive Sheet
Binding Material	Fluorosilicone
Filler Material	Nickel Plated Graphite (Ni/C)
Closing Force	138.1 N/cm ²

Electrical Characteristics

Resistance to Petroleum	Yes
Volume Resistivity (Max)	.05 Ω.cm

Body Features

Gasket Type	Moulded EMI Gasket
Gasket Shape	Sheet

Dimensions

Product Thickness	1.6 mm[.062 in]
-------------------	-----------------

Product Width	300 mm[11.81 in]
---------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-EMIG-0003 Moulded EMI Gasket Conductive Sheet	 TE Part # 2452652-1 SNA Sheet 300mm sq x 1.6mm	 TE Part # 2452698-1 SNA-C Sheet 300mm sq x 1.6mm
---	--	--

Also in the Series | Kemtron 1212 Series



EMI Gaskets(18)

Documents

Product Drawings

[FNG Sheet 300mm sq x 1.6mm](#)

English

Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

[Datasheet - Conductive Elastomers](#)

English

Product Specifications

[Application Specification](#)

English