

# LCCA30329-FT1.5



# Configuration

Connector 1: F MaleConnector 2: N MaleCable Type: LMR-400-75


#### **Features**

- · Using Times Microwave Components
- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity

# **Applications**

- General Purpose
- · Laboratory Use
- Antenna Installations

- PE Jacket
- Low Insertion Loss
- · Bend Radius of 4 Inches
- Land Mobile Radio & Other Communication Systems
- · Cellular & Wi-Fi Systems



## Description

L-com's LCCA30329-FT1.5 is a 75 Ohm low loss F male to N male cable assembly using LMR-400-75 coax, 1.5 FT with Times Microwave components and ships same-day. The LMR-400-75 coax of this F cable uses the PE (F) dielectric with a VoP of 85%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com F to N cable assembly has a male to male gender configuration with 75 Ohm flexible LMR-400-75 series coax and operates to 2.5 GHz. The double shield of this F cable is layered by tinned copper over aluminum tape providing shielding effectiveness greater than 90dB. \*LMR\*\* is a trademark of Times Microwave Systems.

Custom versions of this F male to F male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30329-FT1.5 L-com 75 Ohm Low Loss F Male to N Male Cable Assembly using LMR-400-75 Coax, 1.5 FT with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.



## LCCA30329-FT1.5

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2.5	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Capacitance		15.9 [52.17]		pF/ft [pF/m]
Inductance		0.09 [0.3]		uH/ft [uH/m]
DC Resistance Inner Cond	ductor	2.5 [8.2]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Con-	ductor	1.65 [5.41]		Ohms/1000ft [Ohms/Km]

# **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units	
Frequency	0.05	0.1	0.25	0.5	2.5	GHz	
Insertion Loss (Typ.)	0.21	0.21	0.22	0.2	0.29	dB	

#### **Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

# **Mechanical Specifications**

# **Cable Assembly**

Length 18 in [457.2 mm]
Diameter 0.81 in [20.57 mm]

# Cable

Cable TypeLMR-400-75Impedance75 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Beryllium Copper Dielectric Type PE (F)

Dielectric Type PE (F)
Number of Shields 2
Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper
Jacket Material PE, Black

Jacket Diameter 0.405 in [10.29 mm]

One Time Minimum Bend Radius 1 in [25.4 mm]



# 400-75 Coax, 1.5 FT with Times Microwave Components LCCA30329-FT1.5



Repeated Minimum Bend Radius Bending Moment Flat Plate Crush Tensile Strength 4 in [101.6 mm] 0.5 lbs-ft [0.68 N-m] 40 lbs/in [0.71 Kg/mm] 160 lbs [72.57 Kg]

# **Connectors**

Connector 1	Connector 2		
F Male	N Male		
75 Ohms	75 Ohms		
Beryllium Copper, Gold	Brass, Gold		
	50 μ inch minimum		
PTFE	Teflon		
Brass, Nickel			
Brass, Nickel	Brass, Tri-Metal		
	80 μ inch minimum		
Brass, Nickel	Brass, Tri-Metal		
	80 μ inch minimum		
	F Male 75 Ohms Beryllium Copper, Gold  PTFE Brass, Nickel Brass, Nickel		

# **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C Storage Range -70 to +85 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:



# LCCA30329-FT1.5



## **How to Order**



Example: LCCA30329-12 = 12 inches long cable

LCCA30329-100cm = 100 cm long cable

75 Ohm Low Loss F Male to N Male Cable Assembly using LMR-400-75 Coax, 1.5 FT with Times Microwave Components from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

