



SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer Nylon66 UL94-VO  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-PHB-2x2AW-X-XX	2.00	6.00	4.90
3	XD-PHB-2x3AW-X-XX	4.00	8.00	6.90
4	XD-PHB-2x4AW-X-XX	6.00	10.00	8.90
5	XD-PHB-2x5AW-X-XX	8.00	12.00	10.90
6	XD-PHB-2x6AW-X-XX	10.00	14.00	12.90
7	XD-PHB-2x7AW-X-XX	12.00	16.00	14.90
8	XD-PHB-2x8AW-X-XX	14.00	18.00	16.90
9	XD-PHB-2x9AW-X-XX	16.00	20.00	18.90
10	XD-PHB-2x10AW-X-XX	18.00	22.00	20.90
11	XD-PHB-2x11AW-X-XX	20.00	24.00	22.90
12	XD-PHB-2x12AW-X-XX	22.00	26.00	24.90
13	XD-PHB-2x13AW-X-XX	24.00	28.00	26.90
14	XD-PHB-2x14AW-X-XX	26.00	30.00	28.90
15	XD-PHB-2x15AW-X-XX	28.00	32.00	30.90
16	XD-PHB-2x16AW-X-XX	30.00	34.00	32.90
17	XD-PHB-2x17AW-X-XX	32.00	36.00	34.90
18	XD-PHB-2x18AW-X-XX	34.00	38.00	36.90
19	XD-PHB-2x19AW-X-XX	36.00	40.00	38.90
20	XD-PHB-2x20AW-X-XX	38.00	42.00	40.90
30	XD-PHB-2x30AW-X-XX	58.00	62.00	60.90

Ordering Information

XD - PHB - N \*\*\* - \* - \*\*

Pin Type Colour Contact Plating

			GENERAL TOLERANCE	制图 DRAWING	05	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	PHB (2.00) 双排带扣 弯针	版本 REV.	A
			X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-PHB-2xNAW-X-XX	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						