






剖面 A-A



TYPE 1: riveting(铆合)
Profile B-B



TYPE 3:Fork lock (叉锁)
Profile B-B

Specifications:

规格:

Current rating:1A AC/DC

额定电流: 1A AC/DC

Voltage rating:250V AC

额定电压: 250V AC

Withstanding voltage:1000V AC/MIN

耐受电压: 1000V AC/分钟

Temperature range:-55℃-+105℃

温度范围: -55℃-+105℃

Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

Contact resistance:25mΩMAN

接触电阻:≤25mΩ

Material And FINISHED:

材料和成本:

INSULATOR:PBT+G/F UL 94V-0

绝缘体: PBT+G/F UL 94V-0

SHELL: STEEL

外壳: 钢

CONTACT MATERIAL:BRASS

触点材料: 黄铜

hook:SUS 304

卡勾: 不锈钢

XSC XX F T X X X G
○ ○ ○ ○ ○ ○ ○ ○

○ Series N0.

○ Row No.Pin No:XX-36

○ Welding Board Angle :F-Female

○ T: Traditional

○ Planting Category: 1:Gold 1u ;2:Gold 2u; 3:Gold 3u ;4:Gold 5u; 5:Gold 15u;

6:Gold 30u ;7:Terminal half- Gold Bright Tin;8:Terminal half- Gold 2u Bright Tin

9:Terminal half- Gold 3u Bright Tin;10:Terminal half- Gold 5u Bright Tin

11:Terminal half- Gold 15u Bright Tin;12:Terminal half- Gold 30u Bright Tin

13:Terminal half- Gold Matte Tin;14:Terminal half- Gold 2u Matte Tin

15:Terminal half- Gold 3u Matte Tin;16:Terminal half- Gold 5u Matte Tin

17:Terminal half- Gold 15u Matte Tin;18:Terminal half- Gold 30u Matte Tin

○ B:Black W:White BL:Blue

○ 1:TYPE-1; 3:TYPE-3

○ Special type: blank-No hook; G-Hooked hook

							DSND		SCALE: N/A	MODEL TYPE: SCSi				
ΔX					ANGLAR	±5°		DWN		VIEW:	PART NO.: XSCXXFXXXXG			
ΔX					L≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.: X-XSCXXFXXXXG			
ΔX					4<L≤ 16	±0.3		APPD		SIZE: A4	REVISION			
ΔX					16<L≤ 63	±0.4								
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5								
REVISIONS							UNSPECIFIED TOLERANCES							
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET 1/1	REVISION A0