

Specification Sheet

Part Number: T250I0X2



Engineered and manufactured for maximum performance and quality.
Made from 100% high-quality plastic to ensure efficient recycling.
Inside serration for a strong grip onto bundles.
Easy application either manually or with a tensioning tool.

Heavy Duty Cable Tie, 29" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Article Number	111-00507
Type	T250I
Color	Black (BK)
Quantity Per	bag
Product Description	These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 29" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name	T250I-PA66-BK
------------------	---------------

Minimum Tensile Strength (Imperial)	250.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	1115.0
-----------------------------------	--------

Length L (Imperial)	29.0
---------------------	------

Length L (Metric)	730.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.49
--------------------	------

Width W (Metric)	12.4
------------------	------

Bundle Diameter Min (Imperial)	0.47
--------------------------------	------

Bundle Diameter Min (Metric)	12.0
------------------------------	------

Bundle Diameter Max (Imperial)	8.0
--------------------------------	-----

Bundle Diameter Max (Metric)	203.0
------------------------------	-------

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)