



LCCA30053-FT10

Configuration

Connector 1: SMA MaleConnector 2: SMA FemaleCable Type: RG178

Features

- · Max Frequency 1 GHz
- 70% VoP

Applications

General Purpose

- FEP Jacket
- · Heat Shrink Strain Relief
- · Laboratory Use



Description

L-com's LCCA30053-FT10 is a SMA male to SMA female cable assembly using RG178 coax, 10 FT and ships same-day. The RG178 coax of this SMA cable uses the PTFE dielectric with a VoP of 70%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com SMA to SMA cable assembly has a male to female gender configuration with flexible RG178 series coax and operates to 1 GHz. The shielding of this SMA cable is comprised of silver plated copper braid.

Custom versions of this SMA male to SMA female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30053-FT10 L-com SMA Male to SMA Female Cable Assembly using RG178 Coax, 10 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





LCCA30053-FT10

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.3:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			250	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units	
Frequency	50	100	250	500	1,000	MHz	
Insertion Loss (Max.)	1.35	1.58	2.28	3.26	4.65	dB	

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

 Length
 120 in [304.8 cm]

 Diameter
 0.072 in [1.83 mm]

Cable

Cable TypeRG178Impedance50 OhmsInner Conductor TypeStrandedInner Conductor Material and PlatingCopper, SilverDielectric TypePTFENumber of Shields1

Shield Layer 1 Silver Plated Copper Braid Jacket Material FEP, Tan

Jacket Diameter 0.072 in [1.83 mm]

Repeated Minimum Bend Radius 0.4 in [10.16 mm]





LCCA30053-FT10

Connectors

Description	Connector 1	Connector 2		
Туре	SMA Male	SMA Female		
Specification	MIL-STD-348A	MIL-STD-348		
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold		
Contact Plating Specification	50 µin minimum	MIL-G-45204		
Dielectric Type	PTFE	PTFE		
Body Material and Plating	Brass, Nickel	Brass, Nickel		
Body Plating Specification	100 μin minimum	QQ-N-290		
Coupling Nut Material and Plating	Brass, Nickel			
Coupling Nut Plating Specification	100 μin minimum			
Hex Size	5/16 Inch			
Torque	5 in-lbs 0.57 Nm			

Environmental Specifications

Temperature

Operating Range

-55 to +200 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.





LCCA30053-FT10

How to Order



Example: LCCA30053-12 = 12 inches long cable

LCCA30053-100cm = 100 cm long cable

SMA Male to SMA Female Cable Assembly using RG178 Coax, 10 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

