

# LCCA30256-FT3

# Configuration

- · Connector 1: SMA Male
- · Connector 2: N Female Bulkhead
- Cable Type: LMR-240


#### **Features**

- Using Times Microwave Components
- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity

## **Applications**

- General Purpose
- · Laboratory Use
- · Antenna Installations

- PE Jacket
- · Low Insertion Loss
- · Bend Radius of 2.5 Inches
- Land Mobile Radio & Other Communication Systems
- · Cellular & Wi-Fi Systems



#### Description

L-com's LCCA30256-FT3 is a low loss SMA male to N female bulkhead cable assembly using LMR-240 coax, 3 FT with Times Microwave components and ships same-day. The LMR-240 coax of this SMA cable uses the PE (F) dielectric with a VoP of 84%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com SMA to N cable assembly has a male to female gender configuration with flexible LMR-240 series coax and operates to 5.8 GHz. The double shield of this SMA cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. L-com's RF cable assembly with N bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications. \*LMR<sup>TM</sup> is a trademark of Times Microwave Systems.

Custom versions of this SMA male to SMA female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30256-FT3 L-com Low Loss SMA Male to N Female Bulkhead Cable Assembly using LMR-240 Coax, 3 FT with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





# LCCA30256-FT3

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conduct	or	3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conduc	tor	3.89 [12.76]		Ohms/1000ft [Ohms/Km]
Jacket Spark			5,000	Vrms

# **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.32	0.37	0.44	0.59	0.81	dB

#### **Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

#### **Mechanical Specifications**

#### Cable Assembly

 Length
 36 in [914.4 mm]

 Diameter
 0.81 in [20.57 mm]

 Weight
 0.103 lbs [46.72 g]

#### Cable

Cable TypeLMR-240Impedance50 OhmsInner Conductor TypeSolidInner Conductor Material and PlatingCopperDielectric TypePE (F)Number of Shields2

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid





# LCCA30256-FT3

Jacket MaterialPE, BlackJacket Diameter0.24 in [6.1 mm]

 One Time Minimum Bend Radius
 0.75 in [19.05 mm]

 Repeated Minimum Bend Radius
 2.5 in [63.5 mm]

 Bending Moment
 0.25 lbs-ft [0.34 N-m]

 Flat Plate Crush
 20 lbs/in [0.36 Kg/mm]

 Tensile Strength
 80 lbs [36.29 Kg]

### **Connectors**

Description	Connector 1	Connector 2		
Туре	SMA Male	N Female Bulkhead		
Specification	MIL-STD-348	MIL-STD-348		
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Contact Plating Specification	ASTM B488			
Dielectric Type	Teflon	PTFE		
Outer Conductor Material and Plating		Brass, Tri-Metal		
Body Material and Plating	Passivated Stainless Steel	Brass, Tri-Metal		
Body Plating Specification	SAE-AMS-2700			
Coupling Nut Material and Plating	Passivated Stainless Steel			
Coupling Nut Plating Specification	SAE-AMS-2700			

# **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C Storage Range -70 to +85 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Values at 25°C, sea level.





#### LCCA30256-FT3

#### **How to Order**



Example: LCCA30256-12 = 12 inches long cable

LCCA30256-100cm = 100 cm long cable

Low Loss SMA Male to N Female Bulkhead Cable Assembly using LMR-240 Coax, 3 FT with Times Microwave Components from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

