



Heat Shrink Tubing > RNF100-BK Heat shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **101.6 mm [4 in]**

Recovered Inside Diameter (Max): **50.8 mm [2 in]**

Shrink Ratio: **2:1**

[All RNF100-BK Heat shrink Tubing \(81\)](#)

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.23 mm[.009 in]
Recovered Wall Thickness (Nominal)	1.4 mm[.055 in]
Product Length	1220 mm[48.03 in]
Expanded Inside Diameter (Min)	101.6 mm[4 in]
Recovered Inside Diameter (Max)	50.8 mm[2 in]



Tubing Size Range	50.8 – 101.6 mm[2 – 4 in]
-------------------	---------------------------

Usage Conditions

Shrink Temperature (Min)	95 °C
Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RNF-100




Heat Shrink Tubing(835)



Power Cable Tubing & Accessories(8)

Customers Also Bought




TE Part #813788-000
202A142-3-0



TE Part #2-6609006-3
6EJT1=F8135



TE Part #F75818-000
RNF-100-MINI-SPL-1/4-BK




TE Part #350547-2
UMNL PIN 20-14 AUBR L/P




TE Part #34111
SOLIS R 22-16 COMM 22-18 MIL 8



TE Part #5-1879353-6
RR02 5% 820K AMMO



TE Part #C17298-000
WP-381064-10-9



TE Part #NB09952001
ATUM-19/6-0-STK

NB18442001

Black, 2:1, Single Wall Tubing, Shrinks To 2 in [50.8 mm], Irradiated Modified Polyolefin, 4 in [101.6 mm] Inner Diameter, RAYCHEM RNF-100



Documents

Product Drawings

[RNF-100-4-BK-STK](#)

English

Datasheets & Catalog Pages

[RNF-100 Pages from 9-1773447-9](#)

English

Product Specifications

[Application Specification](#)

English