

Specification Sheet

Part Number: T120RDH0K2



The tie contains a dual locking design to secure two bundles at once. Head design can also provide spacing between parallel bundles. Bent tail allows for quick insertion into head.

Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66, Black, 50/pkg

Article Number 117-05501

Type T120RDH

Color Black (BK)

Quantity Per bag

Product Description The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66, Black, 50/pkg

Global Part Name

T120RDH-PA66-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535.0

Length L (Imperial) 15.7

Length L (Metric) 398.0

Identification Plate Position none

Releasable Closure No

Variant Inside Serrated

Width W (Imperial) 0.3

Width W (Metric) 7.6

Bundle Diameter Min (Imperial) 0.18

Bundle Diameter Min (Metric) 4.6

Bundle Diameter Max (Imperial) 4.0

Bundle Diameter Max (Metric) 100

Bundle Diameter 1st Loop Max (Imperial) 4.0

Bundle Diameter 1st Loop Max (Metric) 101.6

Bundle Diameter 2nd Loop Max (Imperial) 2.0

Bundle Diameter 2nd Loop Max (Metric) 50.8

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Certification/Specification UL-ZODZ2.E64139

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 50

Package Quantity (Metric) 50

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)