

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable
Assembly using 4855R-RD Coax, 10 FT



LCCA30732/RD-FT10

Configuration

- Connector 1: HD-BNC Male
- Connector 2: 1.0/2.3 Male
- Cable Type: Belden 4855R-RD

Features


- Meets SMPTE ST 2082-1
- Backwards Compatible with 2081-1

- 12Gb/s Transmission
- Cost Effective

Applications

- 12G-SDI, Video, and Broadband UHDTV
- Broadband Internet Delivery
- Broadcast A/V

- 4K/8K Video Equipment
- Medical Equipment Requiring High Speed Video
- HD Cameras



Description

L-com's LCCA30732/RD-FT10 is a 75 Ohm 12G SDI HD-BNC male to 1.0/2.3 male cable assembly using 4855R-RD coax, 10 FT and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com HD-BNC to 1.0/2.3 cable assembly has a male to male gender configuration with 75 Ohm flexible Belden 4855R-RD series coax and operates to 12 GHz and enables 12Gb/s data transfer rates for high resolution uncompressed video signal transmission. These products offer 4K and Ultra-HD quality signals that meet SMPTE Standard 2082-1. The shielding of this HD-BNC cable is comprised of aluminum polyester.

Custom versions of this HD-BNC male to HD-BNC male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30732/RD-FT10 L-com 75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable Assembly using 4855R-RD Coax, 10 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
-------------	---------	---------	---------	-------

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable
Assembly using 4855R-RD Coax, 10 FT



LCCA30732/RD-FT10

Frequency Range	DC	12	GHz
VSWR		1.5:1	
Velocity of Propagation	82		%
Group Delay	1.24 [4.07]		ns/ft [ns/m]
Capacitance	16.3 [53.48]		pF/ft [pF/m]
Inductance	0.107 [0.35]		uH/ft [uH/m]
DC Resistance Inner Conductor	19.7 [64.63]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor	3.9 [12.8]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)		300	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	12	GHz
Insertion Loss (Typ.)	0.61	0.79	1.16	1.59	2.5	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length	120 in [304.8 cm]
Diameter	0.5 in [12.7 mm]
Weight	0.3 lbs [136.08 g]

Cable

Cable Type	Belden 4855R-RD
Impedance	75 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	HDPE
Number of Shields	1
Shield Layer 1	Aluminum Polyester
Shield Layer 2	Tinned Copper
Jacket Material	PVC, Red
Jacket Diameter	0.159 in [4.04 mm]

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable
Assembly using 4855R-RD Coax, 10 FT



LCCA30732/RD-FT10

Connectors

Description	Connector 1	Connector 2
Type	HD-BNC Male	1.0/2.3 Male
Impedance	75 Ohms	75 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	10 µin	10 µin
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	Brass, Gold
Outer Conductor Plating Specification	100 µin	3 µin
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin	100 µin minimum
Seal Gasket Material	Silicone	

Environmental Specifications

Temperature

Operating Range -30 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable
Assembly using 4855R-RD Coax, 10 FT



LCCA30732/RD-FT10

How to Order

Part Number Configuration:

LCCA30732/RD - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: LCCA30732/RD-12 = 12 inches long cable
LCCA30732/RD-100cm = 100 cm long cable

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable Assembly using 4855R-RD Coax, 10 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

75 Ohm 12G SDI HD-BNC Male to 1.0/2.3 Male Cable Assembly using 4855R-RD Coax, 10 FT

L-com CAD Drawing

