

## SMA Male Right Angle to Reverse Polarity SMA Male Cable Assembly using RG223 Coax, 5 FT

### LCCA30366-FT5



#### Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Male Reverse Polarity
- Cable Type: RG223

#### Features

- 66% Phase Velocity
- Double Shielded

- PVC Jacket

#### Applications

- General Purpose

- Laboratory Use



#### Description

L-com's LCCA30366-FT5 is a SMA male right angle to reverse polarity SMA male cable assembly using RG223 coax, 5 FT and ships same-day. The RG223 coax of this SMA cable uses the PE dielectric with a VoP of 66%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com SMA to SMA cable assembly has a male to male gender configuration with flexible RG223 series coax. The double shield of this SMA cable is layered by silver plated copper braid over silver plated copper braid. This right angle SMA cable interface on the RG223 coax allows for easier connections in tight spaces.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30366-FT5 L-com SMA Male Right Angle to Reverse Polarity SMA Male Cable Assembly using RG223 Coax, 5 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

SMA Male Right Angle to Reverse Polarity SMA Male  
Cable Assembly using RG223 Coax, 5 FT



## LCCA30366-FT5

### Electrical Specifications

| Description             | Minimum | Typical       | Maximum | Units        |
|-------------------------|---------|---------------|---------|--------------|
| VSWR                    |         |               | 1.5:1   |              |
| Velocity of Propagation |         | 66            |         | %            |
| Capacitance             |         | 30.8 [101.05] |         | pF/ft [pF/m] |
| Operating Voltage (AC)  |         |               | 500     | Vrms         |

### Mechanical Specifications

#### Cable Assembly

|          |                  |
|----------|------------------|
| Length   | 60 in [152.4 cm] |
| Diameter | 0.315 in [8 mm]  |

#### Cable

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | RG223                      |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper, Silver             |
| Dielectric Type                      | PE                         |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Braid |
| Shield Layer 2                       | Silver Plated Copper Braid |
| Jacket Material                      | PVC, Black                 |
| Jacket Diameter                      | 0.209 in [5.31 mm]         |
| One Time Minimum Bend Radius         | 0.984 in [24.99 mm]        |
| Repeated Minimum Bend Radius         | 1 in [25.4 mm]             |

SMA Male Right Angle to Reverse Polarity SMA Male  
Cable Assembly using RG223 Coax, 5 FT



## LCCA30366-FT5

### Connectors

| Description                        | Connector 1          | Connector 2               |
|------------------------------------|----------------------|---------------------------|
| Type                               | SMA Male Right Angle | SMA Male Reverse Polarity |
| Specification                      | MIL-STD-348A         | MIL-STD-348               |
| Impedance                          | 50 Ohms              | 50 Ohms                   |
| Contact Material and Plating       | Brass, Gold          | Gold                      |
| Contact Plating Specification      | 50 µin minimum       | MIL-G-45204               |
| Dielectric Type                    | PTFE                 | PTFE                      |
| Body Material and Plating          | Brass, Nickel        | Brass, Nickel             |
| Body Plating Specification         | 100 µin minimum      | QQ-N-290                  |
| Coupling Nut Material and Plating  | Brass, Nickel        | Brass, Nickel             |
| Coupling Nut Plating Specification | 100 µin minimum      | QQ-N-290                  |
| Hex Size                           | 5/16 inch            | 5/16 inch                 |
| Torque                             | 3 in-lbs 0.34 Nm     | 3 in-lbs 0.34 Nm          |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

SMA Male Right Angle to Reverse Polarity SMA Male  
Cable Assembly using RG223 Coax, 5 FT



## LCCA30366-FT5

### How to Order

Part Number Configuration:

**LCCA30366**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: LCCA30366-12 = 12 inches long cable  
LCCA30366-100cm = 100 cm long cable

SMA Male Right Angle to Reverse Polarity SMA Male Cable Assembly using RG223 Coax, 5 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

SMA Male Right Angle to Reverse Polarity SMA Male Cable Assembly using RG223 Coax, 5 FT

L-com CAD Drawing

