

TE Internal #: 2202508-4
Mini-SAS HD to External Mini-SAS Cable Assembly, 16 Positions,
9.84 ft [3 m], 6 Gb/s, Black Cable, Shielded, 28 AWG, .081 mm²

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Cable Assembly Type: Mini-SAS HD to External Mini-SAS

Equalized: No

Wire Size: .081 mm²

Outside Cable Diameter: 7.87 mm [.31 in]

Features

Product Type Features

Latching Style	Pull Tab Release
Cable Assembly Category	High Speed, Industry Standard
Cable Assembly Type	Mini-SAS HD to External Mini-SAS
Connector Type (End A)	Mini-SAS HD Plug
Connector Type (End B)	External Mini-SAS Plug
Cable Style	Madison TurboTwin, Madison TurboTwin - Round Jacketed

Configuration Features

Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16

Signal Characteristics

Data Rate	6 Gb/s
-----------	--------

Body Features

Shield Material	Aluminum/Polyester Tape/Tin-Plated Copper Braid
-----------------	---



Jacket Material	Flexible PVC
Equalized	No
Cable Color	Black

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Mechanical Attachment

Mating Alignment	Without
------------------	---------

Housing Features

Housing Material	Tin-Plated Zinc Diecast
------------------	-------------------------

Dimensions

Wire Size	.081 mm²
Outside Cable Diameter	7.87 mm[.31 in]

Operation/Application

Shielded	Yes
Halogen Free	Yes

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	3 m[9.84 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUN 2011 (51) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2202508-2
C/A, 4X MINISAS HD TO MINISAS,
28AWG, 1M

Customers Also Bought



TE Part #DTS26F13-04SN
PLUG ASSY



TE Part #9170152001
DWP-125-2-0-STK



TE Part #YDTS24Z25-29PAV001
Jam Nut: D38999, 25-29 Insert, Black
Zinc Nickel Plating



TE Part #YDTS26W21-75BNV001
PLUG ASSY



TE Part #YDTS26Z25-29SBV001
PLUG ASSY



TE Part #ZPF000000000000488
014-1018-20



TE Part #ZPF000000000122869
951-00 R 18-800 P 50-090



TE Part #ZPF000000000122839
014-1094-08

Documents

Product Drawings
C/A, 4X MINISAS HD TO MINISAS, 28AWG, 3M



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2202508-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2202508-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2202508-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-9_MINI_SAS_HD_INTERCONNECT

English