

Specification Sheet

Part Number: 156-01641



Updated 9x17mm oval fir tree design maintains bundle orientation. Fir tree provides low insertion force with high extraction resistance, for easy assembly and reliable performance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

2-Piece Cable Tie/Fir Tree Mount, 8.0" Long, 9–17 mm Mounting Hole, 50lb, PA66HIRHSUV, Black, 3000/ctn

Article Number	156-01641
Type	T50RFT9X17B2
Color	Black (BK)
Quantity Per	carton
Product Description	These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables runing perpendicular to 9x17 oval mounting holes. The fir tree base will easily push into pre-punched holes in panels or threaded blind holes and offers a secure fit. The two-piece design enables the head of the tie to be oriented to the required position to ease assembly, while the disc on top of the fir tree covers the hole and minimizes the ingress of water and dirt.
Short Description	2-Piece Cable Tie/Fir Tree Mount, 8.0" Long, 9–17 mm Mounting Hole, 50lb, PA66HIRHSUV, Black, 3000/ctn

Global Part Name	T50RFT9X17B2-PA66HIRHSUV-BK
------------------	-----------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Fir Tree for oval holes
-----------------	-------------------------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.20
--------------------------------	------

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	2.0
--------------------------------	-----

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.22
--------------------------------	------

Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.5
Mounting Hole Diameter D (Imperial)	0.35 - 0.67
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)