




Heat Shrink Tubing > ATUM 3:1 dual wall heat shrink tubing



Primary Product Color: **Black**

Wall Type: **Dual Wall**

Expanded Inside Diameter (Min): **52 mm [ 2.047 in ]**

Recovered Inside Diameter (Max): **13 mm [ .512 in ]**

Shrink Ratio: **4:1**

[All ATUM 3:1 dual wall heat shrink tubing \(85\)](#)

Features

Product Type Features

Wall Type	Dual Wall
-----------	-----------

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Black
Shrink Ratio	4:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.55 mm[.022 in]
--------------------------------------	-----------------



Recovered Wall Thickness (Nominal)	2.54 mm[.1 in]
Expanded Inside Diameter (Min)	52 mm[2.047 in]
Recovered Inside Diameter (Max)	13 mm[.512 in]
Tubing Size Range	13 – 52 mm[.51 – 2.04 in]

Usage Conditions

Shrink Temperature (Min)	80 °C
Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 110 °C
Recovery Temperature	110 °C

Operation/Application

Mechanical Resistance	Fluids, Mechanical Damage
-----------------------	---------------------------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # EG1114-000  
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM ATUM

Heat Shrink Tubing(220)

Customers Also Bought

TE Part #1-1718492-4  
1.5MM TAB HSG 36 POS ASSY

TE Part #4-968972-1  
MCP2,8 GEH ASSY 12P

TE Part #YDTS20W17-08PNV001  
RECP ASSY

TE Part #HD16-9-96SE  
PLUG ASM





TE Part #5-2297790-2  
2POS,HPF 1.2,REC HSG,ASSY,SLD



TE Part #1456987-1  
2x4 Fem unsealed LP assy Key A




TE Part #2359941-6  
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part #8-1564284-5  
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part #8-1564284-6  
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part #2-2289748-0  
58POS, MIXED,REC HSG,ASSY

Documents

Product Drawings

ATUM-52/13-0-SP

English

Datasheets & Catalog Pages

ATUM Pages from 9-1773447-9

English

Product Specifications

Application Specification

English