



Wire & Cable > Hook Up Wire



Cable Type: **Spec 44**
Voltage Rating: **600 V**
Wire & Cable Insulation Material: **Modified Radiation Cross-linked PVDF**
Conductor Material: **Tin-Coated Copper**
Wire Size: **12 AWG**

Features

Product Type Features

Cable Style	Primary
Product Type	Cable
Product Classification	Cable - High Performance - Spec 44, 55 & RCW

Configuration Features

Number of Conductors	1
Number of Strands	37

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked PVDF
Conductor Material	Tin-Coated Copper
Wire Color (Base)	Black

Dimensions

Overall Outside Diameter	2.74 mm[.108 in]
Wire Diameter	2.74 mm[.108 in]
Conductor Diameter	2.23 mm[.088 in]
Strand Size	28 AWG



Wire Size	12 AWG
-----------	--------

Usage Conditions

Cable Type	Spec 44
Operating Temperature Range	-65 – 150 °C

Other

Wire Source	United States
-------------	---------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 650076-000
[D-436-38](#)

Customers Also Bought




TE Part #175217-3
[DYNAMIC REC CONTACT M L/P](#)




TE Part #5-160447-2
[FF 250 REC 1.0-2.5MM2 TPPB LP](#)




TE Part #969587-2
[MOD2 STIFTLEIS2X5P](#)




TE Part #1-2176348-6
[CRGCQ 2010 330R 5%](#)



TE Part #282238-000
[44A0111-14-2](#)



TE Part #170363-3
[MINI UNIVERSAL M-N-L PIN LP](#)



TE Part #282023-000
[44A0111-20-3](#)



TE Part #AAA7821-00
[91A3-14-06-1-B-HE100](#)



TE Part #2703293001
[TR16-70-0](#)



TE Part #2229636-1
[Eng Samples AER Japan for Harness Assy](#)

Documents

Product Drawings

[44A0111-12-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec9_SPEC44](#)

English

[Raychem Wire and Cable Quick Reference Guide](#)

English



Product Specifications

Product Specification

English