



Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: **CPC Pigtail**

Connector Type (End A): **CPC Receptacle**

Cable Assembly Category: **Industry Standard**

Number of Power Positions: **8**

Number of Signal Positions: **8**

Features

Product Type Features

Cable Assembly Type	CPC Pigtail
Connector Type (End A)	CPC Receptacle
Cable Assembly Category	Industry Standard

Configuration Features

Number of Power Positions	8
Number of Signal Positions	8

Dimensions

Wire Size	24 AWG
-----------	--------

Other

Cable Assembly Configuration	Single Ended
Cable Assembly Length	1 m

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 206434-1
CPC PLUG ASSEMBLY SIZE 11-8

Customers Also Bought

TE Part #1-440129-4
2.0MM,HSG,14POS

TE Part #1-1775469-4
HPI CONN., 2.0MM, R/A, SMT, 14P, 80U

TE Part #1-2273121-5
M12 angled plug to M12 strgt socket AA

TE Part #2292069-1
RCPT ASSEMBLY SMT RA 74 POSN MBC



TE Part #4-2176388-0
RQ 1206 25R5 0.1% 10PPM 5K RL

TE Part #2821385-1
SLIVER C/A, 74P, R/A TO R/A, 10GHZ, 85OHM

TE Part #2-6437158-6
FSN-12A

TE Part #1-6437158-3
FSN-11.5A

TE Part #7-2176269-0
RU 0603 15K 0.01% 2PPM 1K RL

TE Part #4-1879132-0
RN 0402 23K2 0.1% 10PPM 1K RL

Documents

Product Drawings
FL RPT CONN CA,REV,SER 2, SZ 11-8,L 1M
English

CAD Files
Customer View Model
ENG_CVM_CVM_2387132-2_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2387132-2_B.3d_stp.zip
English
Customer View Model
ENG_CVM_CVM_2387132-2_B.2d_dxf.zip
English
3D PDF
3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Circular Plastic Connectors Standard Cable Assemblies
English

Agency Approvals
UL Report
English