

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hybrid cable, Ethernet hybrid CAT5 (100 Mbps), 8-position halogen-free, shielded (Advanced Shielding Technology), Socket straight M12, coding: Y / IP65/IP67, on free cable end, cable length: 2 m, Power with Ethernet (PWE)

Commercial data

Item number	1149277
Packing unit	1 pc
Minimum order quantity	25 pc
Sales key	BF04
Product key	BF1CML
GTIN	4063151144272
Weight per piece (including packing)	255 g
Weight per piece (excluding packing)	255 g
Customs tariff number	85444290
Country of origin	PL

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet hybrid
Number of positions	8
Application	Standard
No. of cable outlets	1
Shielded	yes
Coding	Y

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet hybrid CAT5 (IEC 11801), 100 Mbps

Signaling

Status display	No
Status display present	No

Electrical properties

Nominal voltage U_N	48 V AC (Power and data)
	50 V DC (Power and data)
Nominal current I_N	6 A (Power)
	0.5 A (Data)
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Type	Socket straight M12 / IP65/IP67
Number of positions	8 (4+4)
Coding type	Y (Hybrid)
Shielded	yes
Handle color	black
Material	CuZn (Contact)
	Ni/Au (Contact surface)
	PA (Contact carrier, data)
	PA (Contact carrier, power)
	TPU, hardly inflammable, self-extinguishing (Grip)
Insertion/withdrawal cycles	Zinc die-cast, nickel-plated (Screw connection)
	≥ 100

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP65/IP67
Ambient temperature (operation)	-25 °C ... 90 °C
Number of positions	8
Insertion/withdrawal cycles	100

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	2 m
--------------	-----

Ethernet hybrid [94H]

Dimensional drawing		
UL AWM Style	20233 (80°C/300 V)	
Number of positions	8	
Shielded	yes	
Cable type	Ethernet hybrid [94H]	
Conductor structure	1x4x AWG 26+1x4x AWG 18	
Conductor structure signal line	19x 0.10 mm	
AWG signal line	26	
Conductor cross section	4x 0.15 mm ² (Data)	
	4x 0.85 mm ² (Power)	
Wire diameter incl. insulation	1.05 mm (Data)	
	1.4 mm (Power)	
External cable diameter	8.8 mm ±0.2 mm	
Outer sheath, material	PUR	
External sheath, color	black RAL 9005	
Conductor material	Bare Cu litz wires	
Material wire insulation	PP (Data)	
	PP (Power)	
Single wire, color	white/orange, orange, white/green, green, white, blue, brown, black	
Overall twist	1 star quad and 4 wires with 2 fillers	
Optical shield covering	85 %	
Insulation resistance	≥ 5 GΩ*km	

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Loop resistance	≤ 280.00 Ω/km (Data)
	≤ 45.00 Ω/km (Power)
Wave impedance	100 Ω ±15 Ω (4 MHz ... 100 MHz)
Working capacitance	nom. 50 nF (per kilometer)
Differential impedance	100 Ω ±5 % (at 100 MHz)
Nominal voltage, cable	≤ 125 V (Peak value, not for high-power applications)
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Max. bending cycles	2000000
Tensile strength	85 N (in accordance with DIN EN 50565-1 for flexible installation)
	295 N (in accordance with DIN EN 50565-1 for fixed installation)
Near end crosstalk attenuation (NEXT)	56.3 dB (at 4 MHz)
	50.3 dB (at 10 MHz)
	47.2 dB (at 16 MHz)
	45.8 dB (at 20 MHz)
	42.9 dB (at 31.25 MHz)
	38.4 dB (at 62.5 MHz)
	35.3 dB (at 100 MHz)
Shield attenuation	6.2 dB (at 4 MHz)
	9.8 dB (at 10 MHz)
	12.4 dB (at 16 MHz)
	13.9 dB (at 20 MHz)
	17.6 dB (at 31.25 MHz)
	25.4 dB (at 62.5 MHz)
	32.8 dB (at 100 MHz)
Halogen-free	≥ 80 dB (30 MHz ... 100 MHz)
	according to IEC 60754-1
	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 1581, Section 1060
	in acc. with UL 1581, section 1061
	in accordance with UL 2556, Section 9.3
Resistance to oil	in accordance with IEC 60811-404
	According to DIN EN 50363-10-2
Other resistance	Low adhesion
	Hydrolysis resistance DIN EN 50396
Special properties	Free of substances which would hinder coating with paint or varnish
	Silicone-free
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)

Environmental and real-life conditions

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>


Ambient conditions

Degree of protection	IP65
	IP67
	IP65/IP67

Standards and regulations


Standard designation	M12 connector
Standards/specifications	IEC 61076-2-113

Drawings



M12 hybrid plug pin assignment, 8-pos., Y-coded, pin side view

Dimensional drawing



M12 x 1 socket, straight, shielded


NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Circuit diagram



NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149277>

 UL Listed Approval ID: FILE E 335024				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	56.5 V	0.175 A	-	-

 cUL Listed Approval ID: FILE E 335024				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	56.5 V	0.175 A	-	-

 cUL Listed Approval ID: E221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	6 A	-	-
Data	50 V	0.5 A	-	-

 UL Listed Approval ID: E221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	6 A	-	-
Data	50 V	0.5 A	-	-

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Classifications

ECLASS

ECLASS-11.0	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

NBC-M12FSY/2,0-94H - Hybrid cable



1149277

<https://www.phoenixcontact.com/us/products/1149277>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com