

2205062-2

✓ ACTIVE

Micro-MaTch | Micro-MaTch Industrial

TE Internal #: 2205062-2


MICRO-MATCH MOW Cable Assembly, 8 Positions, .492 ft [.15 m],

Gray Cable, Equalized, 28 AWG, 159.8 – 159.88 mm<sup>2</sup>, Ribbon

Cable, MICRO-MATCH MOW Plug

[View on TE.com >](#)

Cable Assemblies &gt; Copper Cable Assemblies &gt; Pluggable I/O Cable Assemblies &gt; MICRO-MATCH STD MOW TO MOW CABLE ASSY



Cable Assembly Type: MICRO-MATCH MOW

Keyed Position: 1

Equalized: Yes

Wire Size: 159.8 – 159.88 mm<sup>2</sup>[All MICRO-MATCH STD MOW TO MOW CABLE ASSY \(27\)](#)

## Features

### Product Type Features

Cable Assembly Category	Industry Standard
Cable Assembly Type	MICRO-MATCH MOW
Connector Type (End A)	MICRO-MATCH MOW Plug
Connector Type (End B)	MICRO-MATCH MOW Plug
Cable Style	Ribbon Cable

### Configuration Features

Keyed Position	1
Number of Positions	8
Number of Signal Positions	8

### Body Features

Equalized	Yes
Cable Color	Gray
Cable Flammability Rating	UL 2651

### Mechanical Attachment

Mating Alignment	With
------------------	------

### Dimensions

Wire Size	159.8 – 159.88 mm <sup>2</sup>
-----------	--------------------------------

### Operation/Application

Shielded	No
Halogen Free	No

### Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	.15 m [.492 ft]

### Product Compliance


For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts




TE Part # CAT-M5833-F3492A  
Female-on-Board Connector, Top Entry

## Also in the Series | Micro-MaTch Industrial




Board-In Connectors(20)




Insertion & Extraction Tools(1)




PCB Headers & Receptacles(1)



Pluggable I/O Cable Assemblies(52)



Ribbon Cable Connectors(185)



Wire-to-Board Connector Contacts(4)

## Customers Also Bought




TE Part #2205062-3  
MICRO-MATCH STD MOW TO MOW  
CABLE ASSY



TE Part #1-1879463-3  
RL73H 2E R33 1% 5K RL



TE Part #3-1825910-5  
FSM18JH=6MM TACT SWITCH, HIGH  
TEMP



TE Part #3-1879663-6  
H8 249R 0.1% 15PPM



TE Part #4-2176350-0  
CRGCQ 2512 3M3 5%



TE Part #5677904002  
RNF-3000-1.5/0.5-X-SP



TE Part #20015885-02  
FS2030-000X-1500-G



TE Part #8-1393644-0  
V42254B1200C480=PC612 MESSERLE



TE Part #2383945-2  
TERMI-BLOK SMD MOUNT 180\_2P\_3.  
81 MM 12A

## Documents

### Product Drawings

[CA MICRO-MATCH MOW-MOW 8POS](#)

English

---

### Product Specifications

[Application Specification](#)

English

[micro match miniature connector system](#)

English