



Product: [1067A](#)

Inst, 16 Pr #18 Str BC, PVC-NYL Ins E1, OS, Blk PVC Jkt, 600V TC-ER 150V NPLF 90C Dry 75C Wet

 [Request Sample](#)

Product Description

UL Instrumentation, 16 Pair 18AWG (7x26) Bare Copper, PVC-NYL Insulation E1 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 150V NPLF 90C Dry 75C Wet SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications: Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control system (DCS), programmable logic controller (PLC), Solenoids, Valves, Actuators, Positioners

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	16	18	7x26	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC/Nylon - Polyvinyl Chloride + Nylon	0.016 in (0.41 mm)	0.078 in (2.0 mm)	Black, White and Numbered

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.064 in (1.6 mm)	0.793 in (20.1 mm)	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
6.79 Ohm/1000ft	6 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
600 V (TC-ER), 150 V (NPLF)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	Wet/Dry: -30°C to 90°C

Bend Radius

Stationary Min.	Installation Min.
3.16 in (80.3 mm)	3.95 in (100 mm)

Max. Pull Tension: 739 lbs (335 kg)

Bulk Cable Weight: 341 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 UL loading, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, Article 760, NPLF, TC-ER
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ICEA S-73-532, S-61-402

Product Notes

Notes: Alternate color coding available upon request.

History

Update and Revision: Revision Number: 0.528 Revision Date: 04-14-2023

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1067A 0105000	Black	Reel	5,000 ft	612825105701

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.