




Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: CPC Pigtail

Connector Type (End A): CPC Plug

Cable Assembly Category: Industry Standard

Number of Power Positions: 8

Number of Signal Positions: 8

Features

Product Type Features

Cable Assembly Type	CPC Pigtail
Connector Type (End A)	CPC Plug
Cable Assembly Category	Industry Standard

Configuration Features

Number of Power Positions	8
Number of Signal Positions	8

Dimensions

Wire Size	24 AWG
-----------	--------

Other

Cable Assembly Configuration	Single Ended
Cable Assembly Length	1 m

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 206433-1  
CPC RECPT ASSEMBLY SIZE 11-8

Customers Also Bought

TE Part #5747299-8  
15 RCPT SP/FMS INSRT

TE Part #019439-000  
DK-621-0433-1P

TE Part #503123-000  
DK-621-0412-S

TE Part #8-1625868-5  
RP 2A 0.25W 40R2 0.1% 25PPM 1K RL



TE Part #2-2176341-7  
CRGCQ 0805 1K5 1%

TE Part #1-2176342-6  
CRGCQ 0805 330R 5%

TE Part #1-2176343-5  
CRGCQ 1206 150R 1%

TE Part #4-2176378-7  
RQ 0805 30R1 0.1% 10PPM 5K RL

TE Part #YDTS20W11-35SNV001  
RECP ASSY

TE Part #902973-000  
DK-621-0411-P

Documents

Product Drawings  
PLUG CONN CA,REV,SER 2,SZ 11-8,L 1M  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_2387131-2\_B.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2387131-2\_B.3d\_stp.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2387131-2\_B.2d\_dxf.zip  
English

3D PDF  
3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages  
Circular Plastic Connectors Standard Cable Assemblies  
English

Agency Approvals  
UL Report  
English