


18 GHz SMA Female Connector, Solder Attachment, Solder Cup Terminal, 4 Hole Flange Mount, 0.340 inch Hole Spacing



LCCN3114

Configuration

- SMA Female Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- Solder Cup Interface Type
- Solder Attachment
- 4 Hole Flange

Description

The L-com LCCN3114 SMA female connector has a stainless-steel body for telecommunications, data communication, general-purpose test, industrial fields, and rack and panel mount applications. This RF connector has a straight body style and beryllium copper contact with gold-over-copper plating. This threaded standard coaxial connector works on a maximum frequency of 18 GHz and provides an excellent maximum VSWR of 1.25.

The 18 GHz SMA connector is available in a 0.575-inch length, 0.5-inch width, and 0.5-inch height. This straight coaxial connector has 4-hole flange mount with .340-inch hole spacing. The solder cup terminal connector allows developers to configure and customize their signal connections however they desire. This SMA connector with solder attachment has a high-quality construction and an impedance of 50 ohms.

The LCCN3114 solder cup terminal RF connector with 4-hole flange mount has gold-over-nickel body plating. This 18 GHz stainless steel coaxial connector comes with PTFE insulation. The SMA female connector weighs 0.005 pounds and is most used in USB software-defined radio dongles, handheld radios, mobile phone antennas, Wi-Fi antenna systems, and microwave systems.

L-com has the largest in-stock selection of RF and coaxial connectors with same-day shipping for domestic and international orders. We currently have a variety of antenna, audio/video, Ethernet, fiber optic, and USB connectors in our portfolio that are ready to ship today. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the high-quality RF connector that meets your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.25:1	

Mechanical Specifications

Size


Length	0.575in	[14.61mm]
Width/Dia.	0.5in	[12.70mm]
Height	0.5in	[12.7mm]
Weight	0.005lbs	[2.27g]

Material Specifications

Description	Material	Plating
-------------	----------	---------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[18 GHz SMA Female Connector Solder Attachment 4 Hole Flange Mount Solder Cup Terminal, .340 inch Hole Spacing LCCN3114](#)

18 GHz SMA Female Connector, Solder Attachment, Solder Cup Terminal, 4 Hole Flange Mount, 0.340 inch Hole Spacing



LCCN3114

Contact	Beryllium Copper	Gold over Copper MIL-G-45204
Insulation	PTFE	
Body	Stainless Steel	Gold over Nickel MIL-G-45204

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

18 GHz SMA Female Connector, Solder Attachment, Solder Cup Terminal, 4 Hole Flange Mount, 0.340 inch Hole Spacing from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 18 GHz SMA Female Connector Solder Attachment 4 Hole Flange Mount Solder Cup Terminal, .340 inch Hole Spacing LCCN3114

URL: <https://www.l-com.com/18-ghz-sma-female-connector-solder-attachment-4-hole-flange-mount-solder-cup-terminal-.340-inch-hole-spacing-lccn3114-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

