

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13 - Green Dot, 15A, 125V, 14 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P006-L25-HG15



Connects a PC, printer, monitor, scanner or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Heavy-Duty Hospital-Grade Power Cable for Devices That Require a Heavy-Gauge Connection This hospital-grade IEC power cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It is designed for computers, mobile carts, printers, scanners, monitors and other compatible equipment in a hospital or other medical facility and outside patient care vicinities. The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Warranty The P006-L25-HG15 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW

UPC Code

037332224750

Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- 25-ft. (7.62 m) length allows great flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cable replaces or upgrades power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect a mobile cart battery, monitor, computer or printer to a hospital-grade surge protector up to 25-ft. (7.62 m) away in a hospital environment outside patient care vicinities
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-L25-HG15 Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13, 25-ft. (7.62 m), Black

| | |
|--------------------------------------|--|
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 15 |
| Voltage Compatibility (VAC) | 125 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 9.7mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 14 |
| Wire Gauge (OD - mm ²) | 2.08 |
| Cable Length (ft.) | 25 |
| Cable Length (m) | 7.62 |
| Shipping Dimensions (hwd / in.) | 14.17 x 11.81 x 0.50 |
| Shipping Dimensions (hwd / cm) | 35.99 x 30.00 x 1.27 |
| Shipping Weight (lbs.) | 2.58 |
| Shipping Weight (kg) | 1.17 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range | 0% to 65% RH |
| Storage Humidity Range | 0% to 65% RH |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-15P-HG |
| Side B - Connector 1 | IEC-320-C13 - LOCKING |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |

| | |
|-------------------------------------|-------------------------------------|
| High Voltage | No |
| Locking Plug | Yes |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |