

Specification Sheet

Part Number: 126-02204

Arrowhead design makes installation by hand quick and easy without the need for tools.

Ties "clicks" into place upon final installation signaling installer insertion is complete.

Design provides low insertion and high extraction force.



1-Pc Cable Tie/Arrowhead Mount w/Wings, 5.3"L, 50lb, 0.24 - 026" Hole Dia, PA66HIRHS, Black, 500/bg

Article Number	126-02204
----------------	-----------

Type	T50SSL5
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pcs.
--------------	------

Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	1-Pc Cable Tie/Arrowhead Mount w/Wings, 5.3"L, 50lb, 0.24 - 026" Hole Dia, PA66HIRHS, Black, 500/bg
-------------------	---

Global Part Name	T50SSL5-PA66HS-BK
------------------	-------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	5.3
---------------------	-----

Length L (Metric)	135
-------------------	-----

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.0
--------------------------------	-----

Bundle Diameter Max (Metric)	27.0
------------------------------	------

Height H (Imperial)	0.4
Height H (Metric)	10
Panel Thickness Min (Imperial)	0.019
Panel Thickness Max (Imperial)	0.11
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	2.7
Mounting Hole Diameter D (Imperial)	0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.1 - 6.5 mm
Mounting Hole Diameter D Max (Metric)	6.5
Disc Diameter (Imperial)	0.64

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)