

KC-88014450-50,00 - Hybrid cable



1629280

<https://www.phoenixcontact.com/us/products/1629280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hybrid cable, cable length: 50 m, shielded: yes, color of outer sheath: orange RAL 2003



Commercial data

Item number	1629280
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB38
Product key	ABRGCA
GTIN	4055626459585
Weight per piece (including packing)	1,500 g
Weight per piece (excluding packing)	1,500 g
Customs tariff number	85444995
Country of origin	DE

KC-88014450-50,00 - Hybrid cable



1629280

<https://www.phoenixcontact.com/us/products/1629280>

Technical data

Product properties

Product type	Cable by the meter
--------------	--------------------

Connector

Cable specifications

Cable type	HDSLC11Y-J
Transmission speed	CAT5
Transmission speed	100 Mbps (Data interface)
Shielded	yes
Cable structure	(5x 4 + 2x (2x 1.0) + (4x 0.34)C) C
External cable diameter	16.2 mm ±0.5 mm
Outer sheath, material	PUR
Material wire insulation	TPE
External sheath, color	orange RAL 2003
Single wire, color	black 1, black 2, black 3, black 4, green/yellow Power wires + PE brown, violet, black 5, green Signal wires blue, yellow, white, orange Data wires
Nominal voltage, cable	1000 V
Test voltage	4 kV
Rated current	34 A (Power, according to DIN VDE 0298-4 tab. 11/5) 8 A (Signal, according to DIN VDE 0298-4 tab. 11/5) 3.6 A (Data, according to DIN VDE 0298-4 tab. 11/5)
Smallest bending radius, fixed installation	81 mm
Smallest bending radius, movable installation	121 mm
Max. bending cycles	5000000
Traversing path	5 m
Ambient temperature (operation) for fixed installation	-40 °C ... 80 °C
Ambient temperature (operation) for flexible installation	-20 °C ... 60 °C
Special properties	Flexible cable conduit capable
Flame resistance	IEC 60332-1-2
Halogen-free	in accordance with EN 50267-2-1
Resistance to oil	EN 60811-2-1

Cable/line

Cable length	50 m
--------------	------

KC-88014450-50,00 - Hybrid cable



1629280

<https://www.phoenixcontact.com/us/products/1629280>

Classifications

ECLASS

ECLASS-11.0	27060106
ECLASS-12.0	27060106
ECLASS-13.0	27060106

ETIM

ETIM 8.0	EC003250
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

KC-88014450-50,00 - Hybrid cable



1629280

<https://www.phoenixcontact.com/us/products/1629280>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

KC-88014450-50,00 - Hybrid cable

1629280

<https://www.phoenixcontact.com/us/products/1629280>



Accessories

PATG 6/23 - Conductor marker carrier

0808037

<https://www.phoenixcontact.com/us/products/0808037>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 23 x 4 mm

PABA WH/23 - Insert label

1013779

<https://www.phoenixcontact.com/us/products/1013779>



Insert label, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 20

KC-88014450-50,00 - Hybrid cable

1629280


<https://www.phoenixcontact.com/us/products/1629280>



PABA YE/23 - Insert label

1013782

<https://www.phoenixcontact.com/us/products/1013782>



Insert label, Strip, yellow, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 20

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com