




Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies > SFP+ to SFP+ I/O Cable Assembly: 30 AWG



Cable Assembly Type: **SFP+**

Equalized: **No**

Wire Size: **.051 mm²**

Outside Cable Diameter: **4.37 mm [.172 in]**

[All SFP+ to SFP+ I/O Cable Assembly: 30 AWG \(14\)](#)

Features

Product Type Features

Latching Style	Retractable Pin
Cable Assembly Category	High Speed
Cable Assembly Type	SFP+
Connector Type (End A)	SFP+ Plug
Connector Type (End B)	SFP+ Plug
Cable Style	Madison TurboTwin, Madison TurboTwin - Round Jacketed

Configuration Features

Number of Positions	4
Number of Pairs	2
Number of Signal Positions	4

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Signal Characteristics

Data Rate	10 Gb/s
-----------	---------



Body Features

Strain Relief Type	Overmold
Shield Material	Aluminum/Polyester/Aluminum Tape/Tin-Plated Copper Braid
Jacket Material	Flexible PVC
Equalized	No
Cable Color	Black
Cable Flammability Rating	CL2

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Mechanical Attachment

Mating Alignment	Without
------------------	---------

Housing Features

Housing Material	Zinc Alloy
------------------	------------

Dimensions

Wire Size	.051 mm ²
Outside Cable Diameter	4.37 mm[.172 in]

Operation/Application

Shielded	Yes
----------	-----

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	1 m[3.281 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (3.7% in Component part)



MCCP (1.78% in Component part)


Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-SF59-C117ST123 SFP+ Stacked Cage Assemblies	 TE Part # CAT-SF59-C76264 SFP Connectors	 TE Part # 2007135-1 SFP+ 1x4 CageAssembly w/ EMI gasket	 TE Part # 2007180-1 SFP+ 1X2 CAGE ASSM/LIGHTPIPE, EMI GASKET
 TE Part # 2007254-1 SFP+ 1x1 Cage Assembly, Light Pipe	 TE Part # 2198230-2 SFP+ Enhanced 1x2, SAN Heatsink	 TE Part # 2198230-1 SFP+ Enhanced 1x2, PCI Heatsink	 TE Part # 2170030-1 SFP+ 1x4 w/ Ultra Low Profile LP
 TE Part # 2007194-2 SFP+ 1x1 Cage Assembly, PCI, Solder Tail	 TE Part # 2007181-1 SFP+ 1x2 Cage Assy, EMI Gasket	 TE Part # 2007194-1 SFP+ 1x1 Cage Assembly, PCI, Solder Tail	 TE Part # 2007251-1 SFP+ 1x6 Cage Assembly



TE Part # 2007178-1
SFP+ 1x4 Cage Assembly, Light



TE Part # 2007262-1
SFP+ 1x2 Cage Assembly, Light



TE Part # 2198230-3
SFP+ Enhanced 1x2, Networking Heatsink



TE Part # 2007263-1
SFP+ 1x2 Cage Assembly



TE Part # 2007464-3
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part # 2149730-1
SFP+ 1x4 Cage, Heatsinks and Lightpipes



TE Part # 2007464-2
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part # 2007198-2
SFP+ 1x1 Cage Assembly, Press-Fit

Customers Also Bought



TE Part #2333842-6
QSFP 25GIG 26AWG 3 METER



TE Part #1658260-1
RF BOARD TO BOARD ASSY, LOOSE



TE Part #2170024-1
1x4 QSFP Cage Subassy,Thru Bezel



TE Part #2323767-3
DD-DD, 28AWG 2-8PR, 2.0M



TE Part #2323767-4
DD-DD, 28AWG 2-8PR, 2.5M



TE Part #2323766-7
DD-DD, 30AWG 2-8PR, 1.75M



TE Part #2332075-6
C/A, QSFP, 3M, P1-P2, UNEQUALIZED



TE Part #2349967-1
CA, SIDE CCJ TO DYNAMIC

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2127931-2_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2127931-2_F.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2127931-2_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773455-3 - Quick Reference Guide SFP+ Solutions](#)

English

Agency Approvals

[UL Report](#)

English