



Heat Shrink Tubing > TAT125 Heat shrink Tubing



Primary Product Color: **Black**

Wall Type: **Dual Wall**

Expanded Inside Diameter (Min): **6.4 mm [.25 in]**

Recovered Inside Diameter (Max): **3.2 mm [.125 in]**

Shrink Ratio: **2:1**

[All TAT125 Heat shrink Tubing \(52\)](#)

Features

Product Type Features

Wall Type	Dual Wall
-----------	-----------

Body Features

Fluid Type	Aviation Fuel, Brake Fluid, Chemicals /Solvents, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.87 mm[.034 in]
Product Length	1220 mm[48.031 in]
Expanded Inside Diameter (Min)	6.4 mm[.25 in]
Recovered Inside Diameter (Max)	3.2 mm[.125 in]
Tubing Size Range	3.2 – 6.4 mm[.125 – .25 in]

Usage Conditions

--



Shrink Temperature (Min)	95 °C
Resistance Properties	Moisture
Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 110 °C
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Cut-Through, Flexing, Fluids, Mechanical Damage
-----------------------	---

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM TAT-125

Heat Shrink Tubing(56)

Customers Also Bought

TE Part #5-5179180-2
0.8FH,R09H.5,060,08/Sn,TR,SC

TE Part #2-2176306-8
RP 1E 0.1W 2K21 0.1% 25PPM 5K RL

TE Part #NB14002001
TAT125 Heat shrink Tubing


TE Part #NB16024001
RT-375-3/16-X-SP

TE Part #5-212498-1
PLUG ASSY,9C4,AMPLIMITE

TE Part #2007847-3
IMP100S,H,V5P10C,RG,LEW39,5,5

TE Part #2187307-1
TinMan Header Assy 4x16 Open

TE Part #346933-000
2000P-RIBBON-4AG-NAR



Documents

Product Drawings

TAT-125-1/4-0-STK

English

Datasheets & Catalog Pages

TAT Pages from 9-1773447-9

English

Product Specifications

Application Specification

English