



Product: [7892A](#)



Audio Snake Cable, #26-12pr, TC, Indiv. Shielded, CM

Product Description

Digital Audio Snake Cable, CM-Rated, 12-26 AWG tinned copper pairs, Datalene® insulation, individually shielded with Beldfoil® bonded to numbered/color-coded PVC jackets so both strip simultaneously, PVC jacket

Technical Specifications

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Pairs
26	7x34	TC - Tinned Copper	0.019 in	12
Conductor Count:		24		
Total Number of Pairs:		12		

Insulation			
Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene (Foam)	Datalene®	0.054 in	0.0175 in

Color Chart	
Number	Color
1	Brown & Numbered 1
2	Red & Numbered 2
3	Orange & Numbered 3
4	Yellow & Numbered 4
5	Green & Numbered 5
6	Blue & Numbered 6
7	Purple & Numbered 7
8	Gray & Numbered 8
9	White & Numbered 9
10	Black & Numbered 10
11	Tan & Numbered 11
12	Pink & Numbered 12

Inner Shield							
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.019 in	26	Stranded

Table Notes:	Indiv. Foil tapes bonded to inner jacket
--------------	------------------------------------------

Inner Jacket		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.136 in	0.014 in

Outer Shield							
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.019 in	26	Stranded

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.679 in	0.056 in	Yes

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
25.5 Ohm/1000ft	37.3 Ohm/1000ft	37.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12.5 pF/ft	25 pF/ft

Inductance

Nominal Inductance
0.25 µH/ft

Impedance

Nominal Characteristic Impedance
110 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.384 MHz	0.84 dB/100ft
0.7056 MHz	1.14 dB/100ft
0.768 MHz	1.18 dB/100ft
1.024 MHz	1.34 dB/100ft
1.4112 MHz	1.5 dB/100ft
1.536 MHz	1.54 dB/100ft
2.048 MHz	1.69 dB/100ft
2.8224 MHz	1.86 dB/100ft
3.072 MHz	1.92 dB/100ft
4.096 MHz	2.14 dB/100ft
5.6448 MHz	2.4 dB/100ft
6.144 MHz	2.47 dB/100ft
8.192 MHz	2.75 dB/100ft
11.2896 MHz	3.09 dB/100ft
12.288 MHz	3.18 dB/100ft
24.576 MHz	4.2 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
76%

High Frequency

Frequency [MHz]
0.384 MHz
0.7056 MHz
0.768 MHz
1.024 MHz
1.4112 MHz
1.536 MHz
2.048 MHz
2.8224 MHz
3.072 MHz
4.096 MHz
5.6448 MHz
6.144 MHz
8.192 MHz
11.2896 MHz
12.288 MHz
24.576 MHz

Temperature Range

Operating Temperature Range:	-30°C To +80°C
------------------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	150 lbs/1000ft
Max. Pull Tension:	129 lbs
Min. Bend Radius/Minor Axis:	7 in

Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
------------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7892A Z4B2000	Violet	Reel	2,000 ft	612825190776
7892A Z4B1000	Violet Z4B	Reel	1,000 ft	612825433903

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment. Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.
--------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.360 Revision Date: 11-09-2022
----------------------	--------------------------------------------------