



LCCA30344-FT1

Configuration

Connector 1: TNC Male
Connector 2: N Female
Cable Type: LMR-600-DB


Features

- · Using Times Microwave Components
- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 87% Phase Velocity

Applications

- General Purpose
- · Laboratory Use
- · Antenna Installations

- PE Jacket
- · Low Insertion Loss
- · Bend Radius of 6 Inches
- Land Mobile Radio & Other Communication Systems
- · Cellular & Wi-Fi Systems



Description

L-com's LCCA30344-FT1 is a low loss TNC male to N female cable assembly using LMR-600-DB coax, 1 FT with Times Microwave components with heatshrink and ships same-day. The LMR-600-DB coax of this TNC cable uses the PE (F) dielectric with a VoP of 87%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TNC to N cable assembly has a male to female gender configuration with flexible LMR-600-DB series coax and operates to 5.8 GHz. The double shield of this TNC cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. *LMR™ is a trademark of Times Microwave Systems.

Custom versions of this TNC male to TNC female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30344-FT1 L-com Low Loss TNC Male to N Female Cable Assembly using LMR-600-DB Coax, 1 FT with Times Microwave Components with HeatShrink data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





LCCA30344-FT1

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
Velocity of Propagation		87		%
RF Shielding	90			dB
Group Delay		1.17 [3.84]		ns/ft [ns/m]
Capacitance		23.4 [76.77]		pF/ft [pF/m]
Inductance		0.058 [0.19]		uH/ft [uH/m]
DC Resistance Inner Conducto	or	0.53 [1.74]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conduct	or	1.2 [3.94]		Ohms/1000ft [Ohms/Km]
Jacket Spark			8,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units	
Frequency	0.25	0.5	1	2.5	5.8	GHz	
Insertion Loss (Typ.)	0.21	0.21	0.22	0.24	0.27	dB	

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector

Mechanical Specifications

Cable Assembly

 Length
 12 in [304.8 mm]

 Diameter
 0.87 in [22.1 mm]

 Weight
 0.43 lbs [195.04 g]

Cable

Cable TypeLMR-600-DBImpedance50 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Copper Clad Aluminum

Dielectric Type PE (F)
Number of Shields 2

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid



O. P.

LCCA30344-FT1

Jacket Material PE, Black

Jacket Diameter 0.59 in [14.99 mm]

 One Time Minimum Bend Radius
 1.5 in [38.1 mm]

 Repeated Minimum Bend Radius
 6 in [152.4 mm]

 Bending Moment
 2.75 lbs-ft [3.73 N-m]

 Flat Plate Crush
 60 lbs/in [1.07 Kg/mm]

 Tensile Strength
 350 lbs [158.76 Kg]

Connectors

Connector 1	Connector 2		
TNC Male	N Female		
50 Ohms	50 Ohms		
500			
Beryllium Copper, Gold	Spring Bronze, Gold		
PTFE	PTFE		
Outer Conductor Material and Plating			
Brass, Tri-Metal	Copper, Tri-Metal		
Brass, Tri-Metal			
	16 mm		
	TNC Male 50 Ohms 500 Beryllium Copper, Gold PTFE Brass, Tri-Metal		

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C Storage Range -70 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:





LCCA30344-FT1

How to Order



Example: LCCA30344-12 = 12 inches long cable

LCCA30344-100cm = 100 cm long cable

Low Loss TNC Male to N Female Cable Assembly using LMR-600-DB Coax, 1 FT with Times Microwave Components with HeatShrink from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

