



Relays, Contactors & Switches > Contactors > Definite Purpose Contactors



Pole Configuration: 2

Definite Purpose Contactor Coil Voltage Rating: 28 VDC

Definite Purpose Contactor Contact Current Rating: 350 A

Definite Purpose Contactor Mounting Type: Bottom Mount, 2xM5

Definite Purpose Contactor Contact Arrangement: DPST-NO

Features

Product Type Features

Terminal Configuration	2 SPDT-NO
------------------------	-----------

Electrical Characteristics

Coil Voltage (Max)	32 VDC
Definite Purpose Contactor Coil Voltage Rating	28 VDC
Definite Purpose Contactor Coil Resistance	7.8 Ω, 90 Ω
Definite Purpose Contactor Contact Switching Voltage (Max)	600 VAC

Contact Features

Pole Configuration	2
Definite Purpose Contactor Contact Current Rating	350 A
Definite Purpose Contactor Contact Arrangement	DPST-NO

Mechanical Attachment

Definite Purpose Contactor Mounting Type	Bottom Mount, 2xM5
--	--------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 9-1618389-8  
LEV100A5ANG=RELAY, SPST, 24Vdc

Also in the Series | Kilovac EV202


Definite Purpose Contactors(4)

High Voltage Relays(1)

Customers Also Bought



TE Part #788157-2  
SLD CPC PLUG ASSY,13-9,STD SEX




TE Part #796075-1  
NGC SEALING PLUG



TE Part #5-1419102-2  
PCB Power Relay: 30 Amp,  
Monostable DC



TE Part #66360-4  
Pin and Socket Contacts, Type III, LP



TE Part #963292-1  
WIRE SEALING 2,2



TE Part #YDTS20Z17-06PNV001  
RECP ASSY



TE Part #YDTS26Z11-35SNV001  
PLUG ASSY



TE Part #1-1393315-1  
V23132B2002B200=HCR

Documents

Product Drawings

EV202ASAND=Relay, DPST-NO 28V

English

Datasheets & Catalog Pages

5-1773450-5\_sec7\_EV200A

English