

12.4 GHz RP SMA Male Connector Crimp/Solder Attachment for 400 Series, 405 Series, LMR-400, LMR-400-DB, LMR-400-UF, 0.400 inch



LCCN3173

Configuration

- · SMA Male Reverse Polarity Connector
- 50 Ohms
- · Straight Body Geometry

- 400 series, 400 series, 405 series, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Interface Type
- Crimp/Solder Attachment
- 5/16 inch Hex

Description

The L-com LCCN3173 SMA female connector has a brass body for telecommunications, data communication, general-purpose test, industrial fields, and rack and panel mount applications. This RF connector has a straight body style and beryllium copper contact with gold plating. This threaded reverse polarity coaxial connector works on a maximum frequency of 12.4 GHz.

The 12.4 GHz SMA connector is available in a 1.425-inch length, 0.709-inch width, and 0.709-inch height. The 400 series coax connector allows developers to configure and customize their signal connections however they desire. This SMA connector with crimp/solder attachment has a high-quality construction and an impedance of 50 ohms.

The LCCN3173 400 series coax RF connector has gold body plating. This 12.4 GHz brass coaxial connector comes with PTFE insulation. The SMA female connector weighs 0.009 pounds and is most used in USB software-defined radio dongles, handheld radios, mobile phone antennas, Wi-Fi antenna systems, and microwave systems.

L-com has the largest in-stock selection of RF and coaxial connectors with same-day shipping for domestic and international orders. We currently have a variety of antenna, audio/video, Ethernet, fiber optic, and USB connectors in our portfolio that are ready to ship today. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the high-quality RF connector that meets your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz

Mechanical Specifications

Size

Length	1.425in	[36.2mm]
Width/Dia.	0.709in	[18.01mm]
Height	0.709in	[18.01mm]
Weight	0.009lbs	[4.08g]
Mating Torque	3 to 5in-lbs	0.34 to 0.57Nm

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PTFE	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 12.4 GHz RP SMA Male Connector Crimp/Solder Attachment for 400 Series, 405 Series, LMR-400, LMR-400-DB, LMR-400-UF, 0.400 inch LCCN3173



12.4 GHz RP SMA Male Connector Crimp/Solder Attachment for 400 Series, 405 Series, LMR-400, LMR-400-DB, LMR-400-UF, 0.400 inch



LCCN3173

Body	Brass	Gold
Coupling Nut	Brass	Gold

Environmental Specifications

Temperature

Operating Range

-65deg C to +165deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

12.4 GHz RP SMA Male Connector Crimp/Solder Attachment for 400 Series, 405 Series, LMR-400, LMR-400-DB, LMR-400-UF, 0.400 inch from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 12.4 GHz RP SMA Male Connector Crimp/Solder Attachment for 400 Series, 405 Series, LMR-400, LMR-400-DB, LMR-400-UF, 0.400 inch LCCN3173

URL: https://www.l-com.com/12.4-ghz-rp-sma-male-connector-crimp-solder-attachment-400-series-405-series-lmr-400-lmr-400-db-lmr-400-uf-0.400-inch-lccn3173-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

