

Fiber Optic Transceiver, SFP, RJ-45, TM Copper
100 m, AutoNeg 1000M, Wirebale, Arista



FXC-SFP-TXM-1G-ARI

Features

- Operating Data Rates up to 1.25 Gbps
- Distance Range 100 m
- Single 3.3V Power Supply and TTL Logic Interface
- Pluggable SFP RJ-45 Connector
- Standard Temperature Range (available in Industrial Operating Temperatures)
- Compliant with Arista SFP Specification

Applications

- Telecom (Service Providers)
- Datacom
- Enterprise Networks
- Government
- Fiber to the home/business

Description

The L-com FXC-SFP-TXM-1G-ARI is an SFP form-factor transceiver, supporting 1G Ethernet data rate. The L-com FXC-SFP-TXM-1G-ARI supporting 100 m distance and it is Arista compliant transceiver. The L-com FXC-SFP-TXM-1G-ARI features digital diagnostics for performance monitoring of the transceiver. The L-com FXC-SFP-TXM-1G-ARI is one of thousands of fiber optic connectivity products available from L-com in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for your answers on fiber optic connectivity or other L-com products.

Configuration

Data Rate	1.25 Gbps
Form Factor	SFP
Connector	RJ45/RJ48
Distance	0.1 km
Mfg Platform Compatibility	Arista

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Power Supply Voltage	3.15	3.3	3.45	V
Power Supply Current			300	mA
Wattage (Wcc3)			1.04	W

*See table below

Wavelength Channel No.

Size	
Length	2.25 in [57.15 mm]
Weight	0.05 lbs [22.68 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Transceiver, SFP, RJ-45, TM Copper 100 m, AutoNeg 1000M, Wirebale, Arista FXC-SFP-TXM-1G-ARI](#)

Fiber Optic Transceiver, SFP, RJ-45, TM Copper
100 m, AutoNeg 1000M, Wirebale, Arista



FXC-SFP-TXM-1G-ARI

Environmental Specifications

Temperature

Operating Range

0 to +70 deg C

Storage Range

-40 to +85 deg C


Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver, SFP, RJ-45, TM Copper
100 m, AutoNeg 1000M, Wirebale, Arista



FXC-SFP-TXM-1G-ARI




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Fiber Optic Transceiver, SFP, RJ-45, TM Copper 100 m, AutoNeg 1000M, Wirebale, Arista from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

