

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux,
20CH, 100GHz spacing, starting CH40 (1545.32nm), LC/
UPC connectors, with EXP and Mon(1%)



PDW3C-20140-NN46

Features

- Passive
- DWDM
- 100GHz spacing
- 19" Rack Mount
- Two Fiber Mux& Demux Combo
- 20 Channels (40-59)
- Starting with channel 40 (1545.32nm)
- LC/UPC connectors
- Express Channel
- 1% Monitor option

Applications

- Single Mode Fiber Networking
- Dual Fiber
- Side by side Mux and DeMux functions
- 20 channels
- Metro transport
- Regional Distribution
- Inside Plant (ISP) Operation

Description

The L-COM PDW3C-20140-NN46 is a DWDM Passive Filter with 20 DWDM Channels. The L-COM PDW3C-20140-NN46 is a 1RU 19" Rack Mount filter with Combo Mux/DeMux functionality. The L-COM PDW3C-20140-NN46 has 20 DWDM channels: ITU CH40-59 starting with Channel 40 (1545.32nm) and with 100GHz channel spacing. The L-COM PDW3C-20140-NN46 has LC/UPC connectors and has Monitor port option on Mux and Demux. The L-COM PDW3C-20140-NN46 is a dual fiber filter with one sending muxed signal and the other receiving a composit signal for demuxing. L-COM produces the high quality passive filters that your business can rely on. With products continually in stock and same-day shipping, our expert technical support and knowledgeable sales team can get you to the right parts for the job.

Configuration

Connector Type	LC/UPC
Number of Channels	20
Module Function	Mux/DeMux
Filter Type	DWDM

Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Wavelength	1527.22		1564.68	nm
Pass Port Wavelength	1527.22		1564.68	nm
Pass Port Insertion Loss			4	dB
Pass Port Isolation	12			dB
Pass Band	0.68		0.93	nm
Pass Band Ripple			0.5	dB
Center Wavelength (Channel)	1530.33		1545.32	nm
Channel Spacing		0.83		nm
Channel Insertion Loss			4	dB
Return Loss	45			dB
Directivity			50	dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 20CH, 100GHz spacing, starting CH40 \(1545.32nm\), LC/UPC connectors, with EXP and](#)

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux,
20CH, 100GHz spacing, starting CH40 (1545.32nm), LC/
UPC connectors, with EXP and Mon(1%)



PDW3C-20140-NN46

PDL	0.25	dB
PMD	0.2	PS
Power Handling	300	mW
Adjacent Channel Isolation	28	dB
Non-Adjacent Channel Isolation	40	dB
Channel to Monitor Port IL	26	dB
COM to Monitor Port IL	23	dB
IL Thermal Stability	0.005	dB/degC
Wavelength Thermal Stability	0.002	nm/degC

Environmental Specifications

Temperature

Operating Range

-20 to +65 deg C

Storage Range

-40 to +85 deg C

Humidity

5-98 %RH

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Passive DWDM, 1 RU 19" Rack Mount Combo Mux&DeMux, 20CH, 100GHz spacing, starting CH40 (1545.32nm), LC/UPC connectors, with EXP and Mon(1%) from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

