




Product: [1815WB](#)



Audio Snake Cable, 4 Pr #22 Str TC, Ind. Shielded & Jacketed, O/A Foil, PE Jkt, Waterblocked

Product Description

Audio Snake Cable, 4 Pair 22 AWG (7 x 30) Tinned Copper, PP Insulation, Individually Foil Shielded and PVC Jacketed, Overall Beldfoil® Shield, Waterblocking Tape, PE Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio; Below-grade, wet-locations
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	4	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.05 in (1.3 mm)	Black, Red

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC	Individual pair tapes are adhered to their inner jackets for easy stripping

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (19x30) TC

Waterblocking:	Waterblock Tape
----------------	-----------------

Inner Jacket

Element	Material	Nom. Thickness	Nom. Diameter
Pair(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.133 in (3.38 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PE - Polyethylene	0.030 in (0.76 mm)	0.417 in (10.6 mm)	No

Table Notes:	HDPE
Overall Cable Diameter (Nominal):	0.417 in (10.6 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.8 Ohm/1000ft (48.6 Ohm/km)	31 pF/ft (100 pF/m)	56 pF/ft (180 pF/m)	50 Ohm	66%	1.45 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS

## Mechanical Characteristics

### Temperature

Operating
-20°C to +60°C

### Bend Radius

Stationary Min.	Installation Min.
4.2 in (110 mm)	4.2 in (110 mm)

Max. Pull Tension:	109 lbs (49.4 kg)
Bulk Cable Weight:	86 lbs/1000ft (130 kg/km)

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Aerial, Burial
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.339 Revision Date: 11-09-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
1815WB 010500	Black	Reel	500 ft	612825123507
1815WB 0102500	Black	Reel	500 ft	612825431299
1815WB 0101000	Black	Reel	1,000 ft	612825123491

© 2023 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.