




1. 额定值 RATING: 8A 125/250VAC (UL, C-UL)
12A-8 (3) A 250V \sim μ T125/55 (ENEC-17, CQC, CB)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <math>< 50\text{m}\Omega</math>
4. 绝缘电阻 INSULATION RESISTANCE: >100M Ω (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE
6. 所有部件均使用环保材料
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE



Circuit diagram



PANEL CUTOUT

NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	TOLERANCE	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
5		10			DIMENSIONAL TOLERANCES					SCALE	NO			
4		9			RANGE				LMC	MAT'L	***			
3		8		X	± 0.30				2016.05.20	MATERIAL NO.				
2		7		X.X	± 0.20									
1		6		X.XX	± 0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	$\pm 1'$	LEGION ELECTRONIC & HARDWARE CO., LTD.				MFR01-A2F06L1S-R	WIF122007	A0		