



Wire Protection & Management > Cable Glands > EM-EMC2-1SNG613



Cable Gland Product Type: **Cable Gland**  
Cable Gland & Accessory Style: **Standard EMC**  
Primary Product Material: **Brass**  
Clamping Diameter Range: **6. – 12. mm**  
Primary Product Plating Material: **Nickel**

[All EM-EMC2-1SNG613 \(44\)](#)

Features

Product Type Features

Cable Gland Product Type	Cable Gland
Cable Gland & Accessory Style	Standard EMC
Sealable	Yes

Body Features

Primary Product Material	Brass
Primary Product Plating Material	Nickel

Dimensions

Clamping Diameter Range	6. – 12. mm
Thread Length	8 mm

Usage Conditions

Operating Temperature Range	-20 – 100 °C[-4 – 212 °F]
-----------------------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------



Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (3% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought







TE Part #T2010162201-000  
HA-016-F




TE Part #T2020001010-000  
CDM-1.0




TE Part #T1310060120-000  
H6B-TS-M20




TE Part #1SNG601046R0000  
EP-SG-1SNG601



TE Part #1SNG602013R0000  
EM-SG-1SNG602



TE Part #1SNG620016R0000  
EP-ROP-M20-LGR-B



TE Part #T2040063101-000  
HE-006-MS

Documents

Product Drawings  
EM-EMC2-M20-MET-A

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_1SNG613006R0000\_A.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_1SNG613006R0000\_A.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_1SNG613006R0000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages  
Catalog - ENTRELEC Cable Glands

English

Agency Approvals  
UL

English

UL  
English

1SNG613006R0000

Cable Gland, Standard EMC, Brass, 6. – 12. mm Clamping Range, Nickel

