

## Product Datasheet

### SFP-10G-AC10M-C

#### Huawei® Compatible 10Gb/s SFP+ Direct Attach Cable Copper, Active

##### FEATURES

- Available lengths 1m to 15m
- Supports multi-gigabit data rates up to 10.5Gbps
- Supports 1x, 2x, 4x and 8x Fiber Channel data rates
- Hot-pluggable SFP 20PIN footprint
- I/O Connector designed for high-speed differential signal applications
- EMI/EMC performance
- Low Power Consumption < 0.5W
- Power Supply: +3.3V
- Compliant to SFP+ MSA
- Temperature Range: 0~ 70 °C
- ROHS

##### APPLICATIONS

- Storage Area Networks (SAN), Network Attached Storage and Storage Servers
- 1G/2G/4G/8G Fiber Channel
- High capacity I/O in Storage Area Networks, Network Attached Storage, and Storage Servers
- Switched fabric I/O such as ultra-high bandwidth switches and routers
- Data center cabling infrastructure
- High density connections between networking equipment

##### DESCRIPTION

ATGBICS Compatible SFP-10G-AC10M SFP+ Active Copper Cable assemblies are high-performance, cost effective I/O solutions for 10Gb Ethernet and 10G Fiber Channel applications. SFP+ Active copper modules allow hardware manufacturers to achieve high port density, configurability and utilization at a very low cost and to reduce power budget. The high-speed cable assemblies meet and exceed the performance and reliability requirements stipulated by Gigabit Ethernet and Fiber Channel industry standard.

## Product Datasheet

### Recommended Operating Environment:

| Parameter                          | Symbol | Min  | Typical | Max  | Unit |
|------------------------------------|--------|------|---------|------|------|
| <b>Storage Ambient Temperature</b> |        | -40  |         | +85  | °    |
| <b>Operating Case Temperature</b>  | Tc     | 0    |         | +70  | °    |
| <b>Power Supply Voltage</b>        | VCC    | 3.14 | 3.3     | 3.47 | V    |
| <b>Power Dissipation</b>           | PD     |      |         | 0.5  | W    |

### Systems

| Performance                        | Media  |
|------------------------------------|--|
| 10.5 Gpbs line speed, full duplex  | Hot-pluggable, industry-standard Small Form-Factor |
| Bit error rate: better than 10E-12 |  |

### Specifications (Tested under recommended operating conditions, unless otherwise noted)

| Parameter  | Symbol | Min | Type | Max  | Units | Notes |
|--|--------|-----|------|------|-------|-------|
| <b>Electrical characteristics</b>                    |        |     |      |      |       |       |
| <b>Supply Current</b>                                | Icc    | -   | -    | 100  | mA    | 1     |
| <b>Transmitter Differential Input Voltage (PECL)</b> | VIN    | 250 | -    | 1200 | mVpp  |       |
| <b>Receiver Differential Output Voltage (PECL)</b>   | VO     | 185 | -    | 1000 | mVpp  |       |
| <b>Impedance</b>                                     | Zcable | 90  | 100  | 110  | Ohms  |       |
| <b>MOD-DEF1, 2</b>                                   | VIH    | 2.0 | -    | Vcc  | V     |       |

### Note:

1. The supply current includes SFP Module's supply current and test board working current.

## Product Datasheet

### Physical Data

| Parameter             | Description            | 30AWG | 24AWG | Units |
|-----------------------|------------------------|-------|-------|-------|
| <b>Cable Diameter</b> | OD                     | 4.5   | 6.5   | mm    |
| <b>Bend Radius</b>    | Minimum Sustained Bend | 25    | 35    | mm    |

### AWG Information

| Reach @ 10Gb/s (m) | AWG |
|--------------------|-----|
| 7                  | 28  |
| 10                 | 28  |
| 12                 | 24  |
| 15                 | 24  |

## Product Datasheet

### Pin Descriptions

| Pin | Logic      | Symbol   | Name/Description                | Notes |
|-----|------------|----------|---------------------------------|-------|
| 1   |            | VeeT     | Transmitter Ground              |       |
| 2   | LV-TTL-O   | TX_Fault | N/A                             | 1     |
| 3   | LV-TTL-I   | TX_DIS   | Transmitter Disable             | 2     |
| 4   | LV-TTL-I/O | SDA      | Tow Wire Serial Data            |       |
| 5   | LV-TTL-I   | SCL      | Tow Wire Serial Clock           |       |
| 6   |            | MOD_DEF0 | Module present, connect to VeeT |       |
| 7   | LV-TTL-I   | RS0      | N/A                             | 1     |
| 8   | LV-TTL-O   | LOS      | LOS of Signal                   | 2     |
| 9   | LV-TTL-I   | RS1      | N/A                             | 1     |
| 10  |            | VeeR     | Receiver Ground                 |       |
| 11  |            | VeeR     | Receiver Ground                 |       |
| 12  | CML-O      | RD-      | Receiver Data Inverted          |       |
| 13  | CML-O      | RD+      | Receiver Data Non-Inverted      |       |
| 14  |            | VeeR     | Receiver Ground                 |       |
| 15  |            | VccR     | Receiver Supply 3.3V            |       |
| 16  |            | VccT     | Transmitter Supply 3.3V         |       |
| 17  |            | VeeT     | Transmitter Ground              |       |
| 18  | CML-I      | TD+      | Transmitter Data Non-Inverted   |       |
| 19  | CML_I      | TD-      | Transmitter Data Inverted       |       |
| 20  |            | VeeT     | Transmitter Ground              |       |

## Product Datasheet

### Mechanical Information

