

product type designation

product description

IE plug-in cable M12-90/IE FC RJ45

Flexible plug-in cable (4-wire), preferred length, pre-assembled with one 4-pin M12 connector (D-coded, 90° angle) and one IE FC RJ45 plug 180

IE Connecting Cable M12-90/IE FC RJ45 Plug-180; IE FC Trailing cable GP pre-assembled with M12 connector (D-coded) and IE FC RJ45 plug; length 5.0 m.



suitability for use

For connecting Industrial Ethernet stations (e.g. SIMATIC ET200pro, SCALANCE X208PRO and SIMOTION)

cable designation

2YY (ST) CY 2x2x0,75/1,5-100 LI GN

wire length

5 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum

0.063 dB/m
0.213 dB/m

impedance

- at 1 MHz ... 100 MHz

100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz

5 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz

0.5 dB/m

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

66 %

mechanical data

number of electrical cores

4

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

core diameter

- of AWG22 insulated conductor

0.75 mm

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

0.75 mm
1.5 mm
3.9 mm
6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

polyethylene (PE)
PVC
PVC

color

- of the insulation of data wires

white/yellow/blue/orange

<ul style="list-style-type: none"> • of cable sheath 	green
bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible 	32.5 mm
<ul style="list-style-type: none"> • with multiple bends / minimum permissible 	49 mm
<ul style="list-style-type: none"> • with continuous bending 	100 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	68 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation 	-25 ... +75 °C
<ul style="list-style-type: none"> • during storage 	-25 ... +75 °C
<ul style="list-style-type: none"> • during transport 	-25 ... +75 °C
<ul style="list-style-type: none"> • during installation 	-10 ... +60 °C
<ul style="list-style-type: none"> • note 	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	
<ul style="list-style-type: none"> • to mineral oil 	conditional resistance
<ul style="list-style-type: none"> • to grease 	Conditional resistance
<ul style="list-style-type: none"> • to water 	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> • halogen-free 	No
<ul style="list-style-type: none"> • silicon-free 	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval 	Yes
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • RoHS conformity 	Yes
standard for structured cabling	Cat5e
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	No
<ul style="list-style-type: none"> • French marine classification society (BV) 	No
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	No
<ul style="list-style-type: none"> • Germanische Lloyd (GL) 	No
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	No
<ul style="list-style-type: none"> • Nippon Kaiji Kyokai (NK) 	No
<ul style="list-style-type: none"> • Polski Rejestr Statkow (PRS) 	No
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	WG
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	WGB
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

7/7/2022 