

## Data sheet for SINAMICS G120X

Article No. : 6SL3230-1YE24-0UP0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

#### Input

Number of phases	3 AC	
Line voltage	380 ... 480 V +10 % -20 %	
Line frequency	47 ... 63 Hz	
<b>Rated voltage</b>	<b>400V IEC</b>	<b>480V NEC</b>
Rated current (LO)	17.00 A	14.30 A
Rated current (HO)	13.25 A	10.60 A

#### Output

Number of phases	3 AC	
<b>Rated voltage</b>	<b>400V IEC</b>	<b>480V NEC <sup>1)</sup></b>
Rated power (LO)	7.50 kW	10.00 hp
Rated power (HO)	5.50 kW	7.50 hp
Rated current (LO)	18.00 A	14.00 A
Rated current (HO)	13.20 A	11.00 A
Rated current (IN)	18.50 A	
Max. output current	24.00 A	

Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

#### Overload capability

Low Overload (LO)	110% base load current I <sub>L</sub> for 60 s in a 300 s cycle time
High Overload (HO)	150% x base load current I <sub>H</sub> for 60 s within a 600 s cycle time

### General tech. specifications

Power factor λ	0.70 ... 0.85
Offset factor cos φ	0.96
Efficiency η	0.97
Sound pressure level (1m)	63 dB
Power loss <sup>3)</sup>	0.259 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7-1500F)

### Communication

Communication	PROFIBUS DP
---------------	-------------

### Inputs / outputs

#### Standard digital inputs

Number	6
Switching level: 0 → 1	11 V
Switching level: 1 → 0	5 V
Max. inrush current	15 mA

#### Fail-safe digital inputs

Number	1
--------	---

#### Digital outputs

Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0

#### Analog / digital inputs

Number	2 (Differential input)
Resolution	10 bit

#### Switching threshold as digital input

0 → 1	4 V
1 → 0	1.6 V

#### Analog outputs

Number	1 (Non-isolated output)
--------	-------------------------

#### PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C
---

### Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

## Data sheet for SINAMICS G120X

Article No. : 6SL3230-1YE24-0UP0

### Ambient conditions

Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.009 m <sup>3</sup> /s (0.325 ft <sup>3</sup> /s)
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation	-20 ... 45 °C (-4 ... 113 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)
<b>Relative humidity</b>	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible

### Connections

<b>Signal cable</b>	
Conductor cross-section	0.15 ... 1.50 mm <sup>2</sup> (AWG 24 ... AWG 16)
<b>Line side</b>	
Version	screw-type terminal
Conductor cross-section	1.50 ... 6.00 mm <sup>2</sup> (AWG 16 ... AWG 10)
<b>Motor end</b>	
Version	Screw-type terminals
Conductor cross-section	1.50 ... 6.00 mm <sup>2</sup> (AWG 16 ... AWG 10)
<b>DC link (for braking resistor)</b>	
PE connection	On housing with M4 screw
<b>Max. motor cable length</b>	
Shielded	150 m (492.13 ft)
Unshielded	300 m (984.25 ft)

### Mechanical data


Degree of protection	IP20 / UL open type
Frame size	FSB
Net weight	5.83 kg (12.85 lb)
<b>Dimensions</b>	
Width	100 mm (3.94 in)
Height	275 mm (10.83 in)
Depth	218 mm (8.58 in)

### Standards

Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
CE marking	EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

### Converter losses to IEC61800-9-2\*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	37.4 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V

<sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.