

# Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 2 ft. (0.61 m), Red

### MODEL NUMBER: P018-002-ARD











Heavy-duty C14 to C15 power cord connects a PoE network switch or other device with a C16 power inlet to a PDU or UPS system.

#### **Features**

C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge ConnectionThis 250V C15 to C14 cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with highwattage power supplies, and similar network components. This IEC C14 to IEC C15 cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This C15 to C14 power cable features a red SJT jacket and fully molded red ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

#### **Highlights**

- Recommended for powering PoE switches with high-wattage power supplies
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C14 to C15 power cable replaces or upgrades original manufacturer's power cord
- Color-coded red for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

#### **Applications**

- Connect devices like highwattage PoE switches to a PDU up to 2-ft. (0.61 m) away in your data center
- Update or replace the standard power cord provided by a device's original manufacturer
- Extend an existing power connection by 2-ft. (0.61 m)

#### **Package Includes**

 P018-002-ARD IEC C14 to IEC C15 Power Cable, 2-ft. (0.61 m), Red

## **Specifications**

OVERVIEW			
UPC Code	037332199089		
Device Compatibility	Network Switch; UPS; PDU		
Country/Region	North America		
INPUT			
Maximum Input Amps	15		
Voltage Compatibility (VAC)	100-250		
PHYSICAL			



Cable Jacket Color  Cable Jacket Material  Cable Jacket Rating  Power Cord Jacket Type  Cable Outer Diameter (OD)  Number of Conductors  Wire Gauge (AWG)	Red         PVC         VW-1         SJT         9.3mm         3         14	
Cable Jacket Material  Cable Jacket Rating  Power Cord Jacket Type  Cable Outer Diameter (OD)  Number of Conductors  Wire Gauge (AWG)	PVC VW-1 SJT 9.3mm	
Cable Jacket Rating  Power Cord Jacket Type  Cable Outer Diameter (OD)  Number of Conductors  Wire Gauge (AWG)	VW-1 SJT 9.3mm	
Power Cord Jacket Type  Cable Outer Diameter (OD)  Number of Conductors  Wire Gauge (AWG)	SJT 9.3mm 3	
Cable Outer Diameter (OD)  Number of Conductors  Wire Gauge (AWG)	9.3mm 3	
Number of Conductors : Wire Gauge (AWG)	3	
Wire Gauge (AWG)		
	14	
Wire Gauge (OD - mm²)		
1	2.08	
Cable Length (ft.)	2	
Cable Length (m)	0.61	
Cable Length (cm)	60.96	
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.33	
Shipping Weight (kg)	0.15	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	10% to 65% RH	
Storage Humidity Range	10% to 65% RH	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	
Side B - Connector 1	IEC-320-C15	
FEATURES & SPECIFICATIONS		
Antibacterial	No .	
Angled Plug	No	
High Voltage	Yes	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	



WARRANTY & SUPPORT	NTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.