

# 1. Features:

RoHS

- · 28.0×28.0mm Max.(L×W),18.0mm Max. Height.
- · Inductance range: 2.2mH~25.0mH,Custom values are welcomed.
- Ideally used as AC common mode noise filter for TV, VCR, Switch Mode Power Supply, Inverter, Industrial Equipment. attenuation and control unit with better characteristics in low frequency band.
- · Dielectric strength:1500Vrms,winding to winding.
- $\cdot$  UL Class B Compliance Common Mode Chokes.
- $\cdot$  Operating temperature:-55 to +130  $^\circ\!\mathrm{C}$  .
- 2. Mechanical Dimension (Unit:mm):







Side View

Side View

# 3. Electrical Characteristic of DCM282818H Series:

Front View

Part Number	L (mH)	Irate (A)	DCR (Ω)	
	±30%	Max	Max	
DCM282818H-222NHF	2.2	6.0	0.034	
DCM282818H-332NHF	3.3	5.0	0.055	
DCM282818H-502NHF	5.0	4.0	0.085	
DCM282818H-103NHF	10.0	2.5	0.170	
DCM282818H-203NHF	20.0	2.0	0.300	
DCM282818H-253NHF	25.0	1.5	0.430	

4. Impedance vs. Frequency Curve:



US 1 914 347 2474 • Taiwan 886 972 022 388 • Shenzhen 86 755 8418 6263 • Shanghai 86 21 5424 5141 • HK 852 9688 9767 Sales@inter-technical.com • www.inter-technical.com Rev. A, Oct. 10, 2013





### Unit in mm:

Α	В	С	E1	E2	F	G
Max.	Max.	±0.5	±0.5	±0.5	Typical	Max.
28.00	28.00	3.00	25.0	15.0	0.64x0.64	18.0

## **Test Condition:**

- 1.Open Circuit Inductance (OCL) measured at 10KHz, 0.05Vrms, 0 Amp at at 25  $^\circ\!\mathrm{C}$  .
- 2.Irate is defined as the applied current level that cause 35  $^\circ\!C$  temperature rise without force air flow.
- 3.Impedance measures with both windings in parallel and at ambient temperature(25 ℃).