




Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: **CPC Pigtail**

Connector Type (End A): **CPC Plug**

Cable Assembly Category: **Industry Standard**

Number of Power Positions: **7**

Number of Signal Positions: **7**

Features

Product Type Features

Cable Assembly Type	CPC Pigtail
Connector Type (End A)	CPC Plug
Cable Assembly Category	Industry Standard

Configuration Features

Number of Power Positions	7
Number of Signal Positions	7

Dimensions

Wire Size	18 AWG
-----------	--------

Other

Cable Assembly Configuration	Single Ended
Cable Assembly Length	.5 m

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 211401-1
RECEPT,SZ 13-7,CPC

Customers Also Bought

TE Part #3-1879216-2
CPF0402 150K 0.1% 25PPM 1K RL

TE Part #38946-16L
CONT SOC ASSY

TE Part #6-2176306-1
RP 1E 0.1W 4K87 0.1% 25PPM 5K RL

TE Part #D369-P99-NS0
369 9 WAY PLUG, NO CONTACTS, SKT





TE Part #D369-R33-NP0
369 3 WAY REC, NO CONTACTS, PIN



TE Part #D369-R66-NP0
369 6 WAY REC, NO CONTACTS, PIN



TE Part #ZPF000000000203390
787-8055-00



TE Part #675714-000
SO96-3-00



TE Part #EG3238-000
LWB-101-6.0(100)



TE Part #D369-STB-3
369 3 WAY BACKSHELL STRAIGHT
TIE WRAP

Documents

Product Drawings

PLUG CONN CA,STD,SER 1,SZ 13-7,LGTH 0.5M

English

CAD Files

Customer View Model

ENG_CVM_CVM_2387101-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2387101-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2387101-1_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Circular Plastic Connectors Standard Cable Assemblies

English

Agency Approvals

UL Report

English