# General Specifications

### **Electrical Capacity (Resistive Load)**

Logic Level:

0.4VA maximum @ 28V AC/DC maximum (Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)

#### **Other Ratings**

Toggles

Rockers

Keylocks Programmable Illuminated PB Pushbuttons

Rotaries

Slides

Tactiles

÷

Touch

Supplement Accessories Indicators

D

Contact Resistance:	50 milliohms maximum
Insulation Resistance:	500 megohms minimum @ 250V DC
Dielectric Strength:	250V AC minimum between contacts for 1 minute minimum
Mechanical Life:	500,000 operations minimum
Electrical Life:	500,000 operations minimum
Nominal Operating Force:	Standard: 1.5N ±0.5 Newtons
	High: 2.5N ±0.8 Newtons
Stroke:	1.5mm (.059″)

### Materials & Finishes

Actuator:	Silicon rubber
Case:	Polycarbonate resin
Base:	Glass fiber reinforced polyamide resin
Movable Contact:	Silver over nickel with gold plating
Stationary Contacts:	Brass with gold plating
Switch Terminals:	Brass with gold plating

### **Environmental Data**

Operating Temperature Range:	–25°C through +50°C (–13°F through +122°F) for Illuminated –25°C through +70°C (–13°F through +158°F) for Nonilluminated
Humidity:	90 ~ 95% humidity for 96 hours @ 40°C (104°F)
Vibration:	10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning in 1 minute; 3 right angled directions for 2 hours
Shock:	50G (490m/s <sup>2</sup> ) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)
Installation	
Cap Installation Force:	5.0N maximum downward force on actuator

### PCB Processing

Soldering:	Wave Soldering: 270°C maximum @ 6 seconds maximum
	Manual Soldering: 390°C maximum @ 4 seconds maximum
Cleaning:	These devices are not process sealed. Hand clean locally using alcohol based solution.

### **Standards & Certifications**

The NPO1 Series pushbuttons have not been tested for UL recognition or CSA certification. These switches are designed for use in a low-voltage, low-current, logic-level circuit. When used as intended in a logic-level circuit, the results do not produce hazardous energy.

# Distinctive Characteristics

Soft touch actuation achieved by mechanical silicon rubber structure.

Distinct, long stroke of 1.5mm (.059").

Entire cap is fully illuminated with single or bicolor LED.

Compact design with dimension of 12.5mm (.492") from PC board to top of cap.

Alternating legend options with bicolor LED.

Available in both high (2.5N) or standard (1.5N) operating force.

Gold plated contacts provide high reliability.

Crimped terminals ensure secure PC mounting and prevent dislodging during soldering.

Molded-in terminals prevent entry of flux, solvents, and other contaminants.



Actual Size



Tactiles

÷





### DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

#### NP0115HG03LF-JF





Supplement Accessories

### Subminiature Smooth Actuation Pushbuttons

## Series NP01

				Illuminat	ed Models	<b>F</b>		_
		Plunger ( ) = Mo	<b>Position</b> omentary	Connected	d Terminals	Thro	ow & Switch Schematic	_
ole	Model	Normal	Down	-	-	L2, 2, Lamp	n is marked with LC1, 1, L3, L4, L1, LC2. circuit is isolated and requires an nal power source.	_
SP	NP0115AG03L NP0115HG03L	OFF	(ON)	Normally Open	1-2	SPST	↓	
				Nonillumin	ated Models			
		Plunger ( ) = Mo	<b>Position</b> omentary	Connected	l Terminals	Thro	ow & Switch Schematic	-
ole	Model	Normal	Down	-	-	Note: Switch L2, 2,	n is marked with LC1, 1, L3, L4, L1, LC2.	
SP	NP0115AG03N NP0115HG03N	OFF	(ON)	Normally Open	1-2	SPST	1 <b>•</b> 2	
				OPERATII	NG FORC	E		
A   Standard Nominal Operating Force   High Nominal Operating Force     1.5 ±0.5N   2.5 ±0.8N								
	Switch base is Black	¢			S	Switch base is Gray	ý	
			CONTA	CTS, TERM	AINALS, 8	& RATING		-
G03	Gold Contacts		Stro	aight PC Term	ninals	0.4VA	maximum @ 28V AC/DC maximum	_
				ILLUMI	NATION			
L Illuminated Nonilluminated								

### **LED COLORS & SPECIFICATIONS**

LEDs are an integral part of the switch and not available separately. The electrical specifications shown are determined at a basic temperature of 25°C.



If the source voltage exceeds the forward voltage, a ballast resistor is required. Specifications in parentheses ( ) below for Bicolor LED denote simultaneous illumination of Red and Green.

		S	ingle Color LE	D	Bicolor LED								
	ELECTROSTATIC SENSITIVE DEVICES	С	D	F	CF		DG						
D	Color	Red	Amber	Green	Red	Green	Amber	Blue					
	Maximum Forward Current $I_{\rm FM}$	30mA	30mA	25mA	30 (25)mA	25 (25)mA	30mA	30mA					
	Typical Forward Current I <sub>F</sub>	20mA	20mA	16mA	20 (20)mA	16 (5)mA	20mA	20mA					
	Forward Voltage V <sub>F</sub>	1.95V	2.0V	3.3V	1.95V	3.3V	2.0V	3.2V					
0	Maximum Reverse Voltage V <sub>RM</sub>	5V	5V	5V	5V	5V	5V	5V					
	Current Reduction Rate $\Delta I_{F}$	0.41mA/°C above 25°C	0.38mA/°C above 25°C	0.33mA/°C above 25°C	0.40mA/°C above 25°C	0.33mA/°C above 25°C	0.40mA/°C above 25°C	0.40mA/°C above 25°C					
~	Ambient Temperature Range		−25° ~ +50°C			-25° ~	+50°C						
		Red or <sub>LC</sub> Green LEDs <sup>(+)</sup>		• Red/Gree	n (+)		eer/Blue <sup>LC2</sup> ↔ (+) (+) (+) (+) (+) (+) (+)	→ <sup>14</sup> (-) Blue → <sup>13</sup> (-) Amber → <sup>12</sup> (-) Blue					
			CAP TY	PES & COL	ORS								
		(12.0) Sq .472	Cap for S	ingle or Bicolo	r LED								
	AT3022 12mm Square Cap Material: Polycarbonate Resin	(10.2)	JB JC	]	White Diffuser Red Diffuser	JD JF	Clear Lens/Ar Clear Lens/Gr						
	Alternating Legend Cap for Bicolor LED												
	AT3023 12mm Square Cap Material: Polycarbonate Resin	472 (10.2) .402	JCF JDG	Red/Green	e	Clear Le Alternati	ns ng Legend Filte	er					
	Standard Alternating Legend Pairs												
	II O N OFF	12	ON OF	F 13	START	STOP	14 OPE						
	Green/Red	Green/Red			Green/Red		Green/Red						
	or Blue/Amber		or Blue/Amber		or Blue/Ai	mber	or Blue/Amber						
-	Legend	illumination is c Cor d illustrations are	ntact factory fo approximate re	r other Alterna presentations of t	ting Legends.			אואוח					
	U/ ð		www.nkksw	tcnes.com	D78 www.nkkswitches.com								

Slides

Tactiles

÷

Touch

Supplement Accessories Indicators

Toggles

www.nkkswitches.com



снея

## Series NP01

