

## Scope

- The purpose of the document is to specify the functional requirement of a WPC1.2.3\_Qi
   Medium Power Tx Module.
   (WPC1.2.3 is compatible with WPC1.1).
- The Wireless Power supply's Tx Module should meet the ROHS requirement.

## **Applications**

- Smartphone, Mobile phone
- Wearable devices
- Home appliances
- Portable consumer products

# **Product Characteristic**

QPT-0014 is a WPC1.2.3 Qi Medium Power (15W) wireless charging platform: Its transmission efficiency is up to 76% and can provide up to 15W transmission capacity. It enables powering or charging for any WPC-Qi certified products. With fast charging function for Samsung mobile phone.

It adopts intelligent identification system while its transmitter and receiver unit adopts UART (Universal asynchronous receiver/ transmitter) encrypted transmission control signal which is stipulated by WPC1.2.3 The console will process the corresponding power adjustment based on the encoding of the receiving unit. This module has fulfilled the WPC1.2.3 Qi requirement and is certified by Qi.

Multiple LED indication scheme available for options							
	Operational States						
LED	Standby	5W RX	15W RX Samsung Fast Charger	Charge Complete	Fault	Dynamic Power Limiting	
LED1, Red	Off	Off	Off	Off	On	Blink slow	
LED2, Blue	Off	On	Breathing lamp	On	Off	Off	
Standard no LED light, LED1 & LED2 for customer to choose, or design customer LED color.							

# Input Characteristics

Input Voltage & Frequency

ltem	Minimum	Normal	Maximum		
Input Voltage	8.0VDC	12.0VDC	13.0VDC		
	RX Module				
TX Input Voltage	Low Power	Fast Charging	Medium Power		
12.0VDC	V	V	V		
12.0000	v	v	•		
9.0VDC	V	V			

- Input Current
  1.6A Max. @12.0VDC Full load
- Inrush Current (cold)
  2.0A Max. @12.0VDC
  Full load

Full load & ambient temperature @25°C

 Energy Consumption At 11.5VDC or 12.5VDC, energy consumption ≤ 0.03A.



## Output Characteristics (Rx Module)

• Static Output Characteristics (Vo & R+N)

Output Power	Rated Load		Poak Load	Output Range	R + N	
Output Power	Min. Load	Max. Load	Feak Luau	Output Kange		
15W	0.10A	1.25A	1.50A	12V ± 5%	$\leq$ 300m Vp-p	

Note:

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output end paralleled a 0.1uF ceramic capacitor and a 47uF electrolysis capacitor.

• Line & Load Regulation

Output Power	Load Co	ondition	Line Regulation	Load Regulation	
Output Power	Min. Load	Max. Load	Line Regulation		
15W	0.10A	1.25A	± 5%	± 5%	

#### **Protection Requirement**

• Short Circuit Protection

When the output is short circuit to ground, the input power should decrease, the power supply remains undamaged and automatically recover when fault condition is removed.

• Over Current Protection (OCP)

OCP Point Limited: 120%~130% auto restart. The output will be blocked when output is over-current, and should automatically recover when fault condition is removed.

# **Reliability Requirements**

Reliability Test

Test Items	Test Conditions
Storage at high temperature test	+60°C, 16hours
Storage at low temperature test	-20°C, 16hours
Operating at high temperature test	+40°C, 8hours
Operating at low temperature test	-20°C, 8hours
High/Low temperature cycle test	+45°C (2Hrs) → -20°C (2Hrs) → +45°C (2Hrs) → -20°C (2Hrs) continually work 24hours

Burn-in

Burn-in for 2hours at 35°C (±5°C), nominal input voltage, nominal load.

- Vibration Test
  - (1) Amplitude: 2 mm
  - (2) Frequency: 12.4 Hz

(3) Direction: X, Y(4) Time: 30 minutes/pc

- Dropping Test
  - (1) Test height : Determined by weight
  - (2) Drop times: 10 times (one triangle, 3 edge, six surface)
  - (3) Drop platform: 1~2cm thickness solid wood



Equal to or greater than		But les	ss than	Free fall	
lb	Kg	lb	Kg	In	mm
0	0	21	10	30	760
21	10	41	19	24	610
41	19	61	28	18	460
61	28	100	45	12	310
100	45	150	68	8	200

# **Environment Requirement**

- Operating Temperature and Relative Humidity 0°C to +40°C, 20%RH to 80%RH @altitude should be below 10000 feet.
- Storage Temperature and Relative Humidity
  -20°C to +60°C, 10%RH to 90%RH (non-condensing) @altitude should be below 30000 feet.

#### **Execution Standards** (Compatible with these specifications)

- EMC Standards
  EN55022
  EN55024
- WPC1.2.3\_Qi Standards

# **Photo of Product**

Front Side





Back Side





#### Module

• Product Design Proposal

According to the standardization of QI, Please note below 3 points :

- (1) The distance between Tx Coil with PCB and other metal components is Min. 4.5mm.
- (2) The distance between the surface of Tx coil and the surface of product (Working Face) is  $2.0_{-0.5}^{+0.25}$  mm, which means the thickness of the working face plastic is not more than 2.25mm.
- (3) The surface distance between Tx Coil and Rx Coil is 3.0~4.5mm.
- (4) Added cooling device to 22uH inductor to do heat treatment (similar to the computer CPU cooling method).
- (5) In order to pass the EMI, it is recommended to connect the PCBA with the DC 12V power.



PCBA Port Functional Illustration

PCBA : Φ 50(±0.3) \* 4.7(±0.2) mm

Port	JP1-1	JP1-2	VCC	RED	BLUE
Function	BUZZ+	BUZZ-	LED VDD	Red LED-	Blue LED-
Port	GND	D+/D-	VDD	CL1-1	CL1-2
Function	QC3.0/12V GND	QC3.0 D+/D-	QC3.0/12V VDD	Tx	Coil



• Tx Coil Spec



Coil + Shielding : Φ 50 \* 2.25 mm (Max.)

#### Electrical specification @25°C

Parameters	Unit	Limit
Inductance, LS @100kHz, 1.0V, 0.08mm*100 ~10Turns	uH	6.30 ± 10%
Q		40 ± 10%
DCR	mΩ	30 ± 10%

• Aluminum Heat Sink Gauge Spec



(Unit: mm)

#### Others

- Weight : 25 ± 2 g
- Major Test Equipment
  - (1) DC Supply
  - (2) Rx\_Module
  - (3) Electronic Load
  - (4) DPO3014 Digital Phosphor Oscilloscope
  - (5) Logical Analyzer
  - (6) Q110 Qi BST (Base Station Tester)