When precision matters...

# A Tallysman *Accutenna*® TW3870 / TW3872 GPS L1/L2 + GLONASS G1/G2 + BeiDou B1 + Galileo E1

The TW3870/ TW3872 employ Tallysman's unique *Accutenna* technology providing dual band GPS L1/L2, GLONASS G1/G2 + BeiDou B1 + Galileo E1 coverage and is especially designed for precision dual frequency positioning.

The TW3870/TW3872 features a precision tuned, circular dual feed, stacked patch element. The signals from the two orthogonal feeds are combined in a hybrid combiner, amplified in a wide-band LNA, then band-split for narrow filtering in each band and further amplified prior to recombination at the output.

The TW3870/TW3872 offers excellent axial ratio and a tightly grouped phase center variation.

The TW3870/TW3872 covers GPS L2 (1227.6MHz), GLONASS G2 (1248MHz centre), GPS L1/WAAS/EGNOS/MSAS (1575.42MHz), GLONASS G1 (1602MHz, centre), BeiDou B1 and Galileo E1. (1561 and 1589 MHz).

The TW3872 has a pre-filter which increases the antenna's immunity to high amplitude interfering signals, such as LTE and other cellular signals.

The TW3870/TW3872 is housed in a through-hole mount, weather-proof enclosure for permanent installations. L Bracket or Pipe Mount (part numbers 23-0040-0, 23-0065-0 respectively) are available for non-rooftop installation. A 100mm ground plane is recommended for non-roof-top installations.

This product is also available in an OEM formats (TW3865, TW3870E, TW3872E, and TW3868)

#### **Applications**

Tallysman

- Precision GPS position
- Dual Frequency RTK receivers
- Mission Critical GPS Timing
- Military & Security
- Network Timing and Synchronization

#### Features

- Very low Noise Preamp, < 2dB
- Axial ratio L1: ≤1 dB typ. 1.5 dB max.
- Tight Phase Center Variation
- LNA Gain 35 dB typ.
- Low current: 24 mA typ.
- ESD circuit protection: 15 KV
- Invariant performance from: +2.5 to 16VDC

#### **Benefits**

- Ideal for L1/L2 RTK surveying systems
- Great multipath rejection
- Increased system accuracy
- Great signal to noise ratio
- IP67, REACH, and RoHS compliant



TW3870 Dimensions (mm)



When precision matters...

## TW3870 / TW3872 GPS L1/L2 + GLONASS G1/G2 + BeiDou B1 + Galileo E1

**Specifications** (Measured a Vcc = 3V, and Temperature=25°C)

Antenna			
Patch Architecture	Circular, Dual Feed, Dual Stacked Patch		
L2 Gain (100mm ground plane), 1227.6-1246MHz	3.8 dBic Min at Zenith on 100mm Ground Plane		
L1 Gain (100mm ground plane), 1575.42MH-1606MHz	4.5 dBic Min at Zenith on 100mm Ground Plane		
Axial Ratio, L1/G1/E1/B1, L2/G2	≤ 1.0 dB typ. 1.5 dB max.; ≤1.5 dB typ. 2.0 dB max.		
1dB Bandwidth,	L2: 1227MHz-1250MHz L1: 1557MHz-1606MHz		
Polarization	RHCP,		
Electrical			
Bandwidth L2: 1213MH	z-1261MHz (Filter bandwidth) L1: 1557 MHz-1606MHz (Fil		

Bandwidth	L2: 1213MH	L2: 1213MHz-1261MHz (Filter bandwidth) L1: 1557 MHz-1606MHz (Filter bandwidth)		
Overall LNA Gain		35dB typ, 32 dE	B min, each of L1 and L2 Bands,	
Gain Variation with Temperature.		3dB max over o	operational temperature range	
LNA Noise Figure		1.5dB typ at 25	5°C (TW3870) 2.5dB typ @25°C (TW3872)	
VSWR (at LNA output)		<1.5:1 typ. 1.8:	:1 max.	
Supply Voltage Range		+2.5 to 16VDC 1	nominal, up to 50mV p-p ripple	
EMI Immunity		50V/Meter, exc	cepting L1+/-100MHz and L2 +/- 100MHz	
Supply Current		24 mA typ. at 2	:5°C, 25mA max at 75°C.	
ESD Circuit protection		15 KV air disch	arge.	
Out-of-Band Rejection L1		L2		
<1450 MHz	>40 dB	<1130 MHz	>40 dB	
<1520 MHz	>30 dB	<1190 MHz	>30 dB	
>1650 MHz	>35 dB	>1284 MHz	>32 dB	

#### **Mechanicals & Environmental**

Mechanical Size, Ground Plane
Operating Temperature Range
Enclosure
Weight
Attachment Method
Environmental
Shock
Vibration
Salt fog / spray

Tallysman

66mm x 21mm (see drawing on other page), 100mm ground plane recommended -40°C to +85°C Radome: EXL9330, Base: Zamak White Metal 185 g Permanent <sup>3</sup>/<sub>4</sub>" (19mm) through hole mount IP67, RoHS, REACH, and RED compliant Vertical axis: 50 G, other axes: 30 G 3 axis, sweep = 15 min, 10 to 200 Hz sweep: 3 G MIL-STD-810F Section 509.4

### **Ordering Information**

TW3870 – GPS L1/L2 + GLONASS G1/G2 + BeiDou B1 + Galileo E1 33-3870-xx-yy-zzzz TW3872 - GPS L1/L2 + GLONASS G1/G2 + BeiDou B1 + Galileo E1 33-3872-xx-yy-zzzz Where xx = connector type, yy = shape and colour of radome and <math>zzzz = cable length in mm (where applicable)

Please refer to the Ordering Guide [ http://www.tallysman.com/wp-content/uploads/Current-Ordering-Guide.pdf] for the current and complete list of available radomes and connectors.



Tel +1 613 591 3131



36 Steacie Drive, Ottawa ON K2K 2A9 Canada Fax 613 591 3121 sales@tallysman.com

The information provided herein is intended as a guide only and is subject to change without notice. This document is not to be regarded as a guarantee of performance. Tallysman Wireless Inc. hereby disclaims any or all warranties and liabilities of any kind. © 2010 Tallysman Wireless Inc. All rights reserved. Rev 4.4